

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273569

Luminaire Tested: P3AS05R709830DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273569
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R709830DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R70 optic, 3000K CCT AND, 98CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 266.0 lumens
Efficiency: N/A
Efficacy: 36.9 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273569

CATALOG NUMBER: P3AS05R709830DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1273569

CATALOG NUMBER: P3AS05R709830DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	88	83	98	92	87	83	89	85	81		87	83	80		84
4	95	86	80	76	93	85	80	75	83	78	74		81	77	73		79
5	89	80	74	69	88	79	73	69	78	72	68		76	71	68		74
6	85	75	68	64	83	74	68	64	73	67	63		71	66	63		70
7	80	70	64	59	79	69	63	59	68	62	58		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	51		58
10	69	58	52	48	67	58	52	48	57	51	48		56	51	48		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	62385
5°	61237
10°	57759
15°	52418
20°	45854
25°	38664
30°	31676
35°	24574
40°	17576
45°	11133
50°	5561
55°	3403
60°	2938
65°	2698
70°	2372
75°	2203
80°	1894
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11133 cd/sqm

TEST NUMBER: P1273569

CATALOG NUMBER: P3AS05R709830DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	26.0	9.8
10°-20°	64.2	24.1
20°-30°	73.2	27.5
30°-40°	57.2	21.5
40°-50°	28.1	10.6
50°-60°	8.7	3.3
60°-70°	5.1	1.9
70°-80°	2.7	1.0
80°-90°	0.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	163.4	61.4
0°-40°	220.6	82.9
0°-60°	257.4	96.7
0°-90°	266.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	266.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	284	
5°	278	26
15°	231	64
25°	160	73
35°	92	57
45°	36	28
55°	9	9
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1273569

CATALOG NUMBER: P3AS05R709830DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	284.5
2.5°	283.1
5°	278.2
7.5°	270.5
10°	259.4
12.5°	246.4
15°	230.9
17.5°	214.2
20°	196.5
22.5°	178.0
25°	159.8
27.5°	142.1
30°	125.1
32.5°	108.0
35°	91.8
37.5°	76.2
40°	61.4
42.5°	47.7
45°	35.9
47.5°	25.2
50°	16.3
52.5°	10.7
55°	8.9
57.5°	7.8
60°	6.7
62.5°	5.9
65°	5.2
67.5°	4.4
70°	3.7
72.5°	3.0
75°	2.6
77.5°	2.2
80°	1.5
82.5°	1.1
85°	0.7
87.5°	0.4
90°	0.0

(END OF REPORT)