

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273684

Luminaire Tested: P3AS09R309830DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273684
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R309830DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R30 optic, 3000K CCT AND, 98CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 445.9 lumens
Efficiency: N/A
Efficacy: 40.5 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273684
CATALOG NUMBER: P3AS09R309830DE010 E3DLD1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1273684

CATALOG NUMBER: P3AS09R309830DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91			
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	89	87	85	83			
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	84	80	78	76			
4	94	86	79	74	92	84	79	74	82	77	73	80	76	72	78	74	71	70			
5	89	79	73	68	87	78	72	68	77	71	67	75	70	66	73	69	66	64			
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59			
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55			
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53	51			
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48			
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	105364
5°	102993
10°	95790
15°	85222
20°	73296
25°	62108
30°	51552
35°	40448
40°	28969
45°	19010
50°	10814
55°	7111
60°	6710
65°	6226
70°	5642
75°	5083
80°	4799
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 19010 cd/sqm



TEST NUMBER: P1273684

CATALOG NUMBER: P3AS09R309830DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.4	9.7
10°-20°	104.4	23.4
20°-30°	117.6	26.4
30°-40°	93.9	21.1
40°-50°	48.3	10.8
50°-60°	18.2	4.1
60°-70°	11.9	2.7
70°-80°	6.4	1.4
80°-90°	1.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	265.4	59.5
0°-40°	359.4	80.6
0°-60°	425.8	95.5
0°-90°	445.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	445.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	480	
5°	468	43
15°	375	104
25°	257	118
35°	151	94
45°	61	48
55°	19	18
65°	12	12
75°	6	6
85°	2	2
90°	0	



TEST NUMBER: P1273684
CATALOG NUMBER: P3AS09R309830DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	480.5
1°	480.5
2°	478.9
3°	476.1
4°	472.3
5°	467.9
6°	462.5
7°	455.3
8°	447.7
9°	438.9
10°	430.2
11°	420.3
12°	409.9
13°	399.0
14°	387.5
15°	375.4
17.5°	344.8
20°	314.1
22.5°	284.6
25°	256.7
27.5°	229.3
30°	203.6
32.5°	177.3
35°	151.1
37.5°	125.3
40°	101.2
42.5°	79.9
45°	61.3
47.5°	45.4
50°	31.7
52.5°	22.4
55°	18.6
57.5°	17.0
60°	15.3
62.5°	13.7
65°	12.0
67.5°	10.4
70°	8.8
72.5°	7.1
75°	6.0
77.5°	4.9
80°	3.8
82.5°	2.7
85°	1.6
87.5°	0.5



TEST NUMBER: P1273684
CATALOG NUMBER: P3AS09R309830DE010 E3DLD1WMH

CANDELA DISTRIBUTION (continued):

90° | $\frac{0^\circ}{0.0}$

(END OF REPORT)