

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273712

Luminaire Tested: P3AS09R359830DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273712
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R359830DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R35 optic, 3000K CCT AND, 98CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 442.0 lumens
Efficiency: N/A
Efficacy: 40.2 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273712

CATALOG NUMBER: P3AS09R359830DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1273712

CATALOG NUMBER: P3AS09R359830DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96
2	106	100	96	92	104	98	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	75	72		78
5	89	79	73	68	87	78	72	67	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	61		70	65	61		68
7	79	69	62	57	78	68	62	57	67	61	57		65	60	57		64
8	75	64	58	53	74	64	57	53	63	57	53		62	56	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	51	46	66	56	50	46	56	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	100957
5°	98833
10°	92561
15°	83088
20°	72270
25°	61576
30°	51578
35°	41091
40°	29713
45°	18793
50°	10234
55°	7111
60°	6710
65°	6226
70°	5963
75°	5083
80°	4799
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18793 cd/sqm

TEST NUMBER: P1273712

CATALOG NUMBER: P3AS09R359830DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.8	9.5
10°-20°	101.8	23.0
20°-30°	116.7	26.4
30°-40°	95.2	21.6
40°-50°	48.0	10.9
50°-60°	17.8	4.0
60°-70°	12.0	2.7
70°-80°	6.6	1.5
80°-90°	2.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	260.3	58.9
0°-40°	355.6	80.5
0°-60°	421.4	95.3
0°-90°	442.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	442.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	460	
5°	449	42
15°	366	102
25°	254	117
35°	154	95
45°	61	48
55°	19	18
65°	12	12
75°	6	7
85°	2	2
90°	0	

TEST NUMBER: P1273712

CATALOG NUMBER: P3AS09R359830DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	460.4
1°	459.9
2°	458.8
3°	456.6
4°	453.3
5°	449.0
6°	443.5
7°	438.0
8°	430.9
9°	423.8
10°	415.7
11°	406.9
12°	397.6
13°	387.3
14°	376.3
15°	366.0
17.5°	338.1
20°	309.7
22.5°	280.7
25°	254.5
27.5°	228.9
30°	203.7
32.5°	178.6
35°	153.5
37.5°	128.4
40°	103.8
42.5°	80.8
45°	60.6
47.5°	43.7
50°	30.0
52.5°	21.8
55°	18.6
57.5°	16.9
60°	15.3
62.5°	13.7
65°	12.0
67.5°	10.4
70°	9.3
72.5°	7.6
75°	6.0
77.5°	4.9
80°	3.8
82.5°	2.7
85°	1.6
87.5°	1.1



TEST NUMBER: P1273712

CATALOG NUMBER: P3AS09R359830DE010 E3DLD1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)