

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272673

Luminaire Tested: P3AS20R359827D010 E3DLD1H

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1272673  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS20R359827D010 E3DLD1H  
Description: 3in Adjustable LED luminaire with, R35 optic, 2700K CCT AND, 98CRI , E3DLD1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1151.0 lumens  
Efficiency: N/A  
Efficacy: 42.0 lumens/watt  
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 27.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1272673

CATALOG NUMBER: P3AS20R359827D010 E3DLD1H

### Luminous Intensity Polar Plot



TEST NUMBER: P1272673

CATALOG NUMBER: P3AS20R359827D010 E3DLD1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 112 | 109 | 106 | 104 | 110 | 107 | 104 | 102 | 103 | 101 | 99  |  | 99  | 98  | 96  |  | 96  |
| 2   | 106 | 100 | 96  | 92  | 104 | 98  | 94  | 91  | 95  | 92  | 89  |  | 92  | 89  | 87  |  | 89  |
| 3   | 100 | 92  | 87  | 82  | 98  | 91  | 86  | 81  | 88  | 84  | 80  |  | 86  | 82  | 79  |  | 83  |
| 4   | 94  | 85  | 79  | 74  | 92  | 84  | 78  | 74  | 82  | 77  | 73  |  | 80  | 75  | 72  |  | 78  |
| 5   | 89  | 79  | 73  | 68  | 87  | 78  | 72  | 67  | 76  | 71  | 67  |  | 75  | 70  | 66  |  | 73  |
| 6   | 84  | 74  | 67  | 62  | 82  | 73  | 67  | 62  | 71  | 66  | 61  |  | 70  | 65  | 61  |  | 68  |
| 7   | 79  | 69  | 62  | 57  | 78  | 68  | 62  | 57  | 67  | 61  | 57  |  | 65  | 60  | 57  |  | 64  |
| 8   | 75  | 64  | 58  | 53  | 74  | 64  | 57  | 53  | 63  | 57  | 53  |  | 62  | 56  | 53  |  | 61  |
| 9   | 71  | 60  | 54  | 50  | 70  | 60  | 54  | 50  | 59  | 53  | 49  |  | 58  | 53  | 49  |  | 57  |
| 10  | 67  | 57  | 51  | 46  | 66  | 56  | 50  | 46  | 56  | 50  | 46  |  | 55  | 50  | 46  |  | 54  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 262918 |
| 5°  | 257362 |
| 10° | 241011 |
| 15° | 216346 |
| 20° | 188200 |
| 25° | 160364 |
| 30° | 134324 |
| 35° | 106997 |
| 40° | 77345  |
| 45° | 48966  |
| 50° | 26677  |
| 55° | 18504  |
| 60° | 17455  |
| 65° | 16240  |
| 70° | 15515  |
| 75° | 13217  |
| 80° | 12628  |
| 85° | 10819  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 48966 cd/sqm

TEST NUMBER: P1272673

CATALOG NUMBER: P3AS20R359827D010 E3DLD1H

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 108.8  | 9.5       |
| 10°-20°   | 265.2  | 23.0      |
| 20°-30°   | 303.9  | 26.4      |
| 30°-40°   | 248.0  | 21.5      |
| 40°-50°   | 125.0  | 10.9      |
| 50°-60°   | 46.5   | 4.0       |
| 60°-70°   | 31.1   | 2.7       |
| 70°-80°   | 17.2   | 1.5       |
| 80°-90°   | 5.2    | 0.5       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 677.9  | 58.9      |
| 0°-40°    | 925.9  | 80.4      |
| 0°-60°    | 1097.4 | 95.3      |
| 0°-90°    | 1151.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1151.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1199 |      |
| 5°  | 1169 | 109  |
| 15° | 953  | 265  |
| 25° | 663  | 304  |
| 35° | 400  | 248  |
| 45° | 158  | 125  |
| 55° | 48   | 46   |
| 65° | 31   | 31   |
| 75° | 16   | 17   |
| 85° | 4    | 5    |
| 90° | 0    |      |

TEST NUMBER: P1272673

CATALOG NUMBER: P3AS20R359827D010 E3DLD1H

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1199.0 |
| 1°    | 1197.6 |
| 2°    | 1194.8 |
| 3°    | 1189.1 |
| 4°    | 1180.5 |
| 5°    | 1169.2 |
| 6°    | 1154.9 |
| 7°    | 1140.7 |
| 8°    | 1122.2 |
| 9°    | 1103.7 |
| 10°   | 1082.4 |
| 11°   | 1059.6 |
| 12°   | 1035.5 |
| 13°   | 1008.4 |
| 14°   | 980.0  |
| 15°   | 953.0  |
| 17.5° | 880.4  |
| 20°   | 806.5  |
| 22.5° | 731.1  |
| 25°   | 662.8  |
| 27.5° | 596.0  |
| 30°   | 530.5  |
| 32.5° | 465.1  |
| 35°   | 399.7  |
| 37.5° | 334.2  |
| 40°   | 270.2  |
| 42.5° | 210.5  |
| 45°   | 157.9  |
| 47.5° | 113.8  |
| 50°   | 78.2   |
| 52.5° | 56.9   |
| 55°   | 48.4   |
| 57.5° | 44.1   |
| 60°   | 39.8   |
| 62.5° | 35.6   |
| 65°   | 31.3   |
| 67.5° | 27.0   |
| 70°   | 24.2   |
| 72.5° | 19.9   |
| 75°   | 15.6   |
| 77.5° | 12.8   |
| 80°   | 10.0   |
| 82.5° | 7.1    |
| 85°   | 4.3    |
| 87.5° | 2.8    |



TEST NUMBER: P1272673  
CATALOG NUMBER: P3AS20R359827D010 E3DLD1H

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)