

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273716

Luminaire Tested: P3AS09R359830DE010 E3DLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273716
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R359830DE010 E3DLP1MW
Description: 3in Adjustable LED luminaire with, R35 optic, 3000K CCT AND, 98CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 355.0 lumens
Efficiency: N/A
Efficacy: 32.3 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273716
CATALOG NUMBER: P3AS09R359830DE010 E3DLP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1273716
 CATALOG NUMBER: P3AS09R359830DE010 E3DLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93				93
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86				86
3	102	95	90	86	100	94	89	85	91	87	84	89	85	82	86	84	81	80				80
4	97	89	83	79	95	88	82	78	86	81	77	84	80	77	82	78	76	74				74
5	92	83	77	73	90	82	77	73	81	76	72	79	75	71	77	74	71	69				69
6	87	78	72	68	86	77	72	68	76	71	67	75	70	67	73	69	66	65				65
7	83	74	68	63	82	73	67	63	72	67	63	71	66	63	69	65	62	61				61
8	79	70	64	60	78	69	63	59	68	63	59	67	62	59	66	62	59	57				57
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54				54
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	56	53	51				51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	114114
5°	111292
10°	101757
15°	86357
20°	68373
25°	51705
30°	37651
35°	25458
40°	15658
45°	8993
50°	5424
55°	4396
60°	3815
65°	3424
70°	2821
75°	2796
80°	2778
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8993 cd/sqm



TEST NUMBER: P1273716
 CATALOG NUMBER: P3AS09R359830DE010 E3DLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.7	13.2
10°-20°	104.9	29.5
20°-30°	98.1	27.6
30°-40°	60.1	16.9
40°-50°	23.7	6.7
50°-60°	10.4	2.9
60°-70°	6.5	1.8
70°-80°	3.5	1.0
80°-90°	1.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	249.7	70.3
0°-40°	309.8	87.3
0°-60°	343.9	96.9
0°-90°	355.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	355.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	520	
5°	506	47
15°	380	105
25°	214	98
35°	95	60
45°	29	24
55°	12	10
65°	7	7
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1273716
CATALOG NUMBER: P3AS09R359830DE010 E3DLP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	520.4
1°	520.9
2°	519.3
3°	516.0
4°	511.1
5°	505.6
6°	498.5
7°	490.3
8°	480.5
9°	469.5
10°	457.0
11°	443.8
12°	429.6
13°	414.3
14°	397.4
15°	380.4
17.5°	336.7
20°	293.0
22.5°	250.9
25°	213.7
27.5°	179.3
30°	148.7
32.5°	120.3
35°	95.1
37.5°	72.7
40°	54.7
42.5°	39.4
45°	29.0
47.5°	20.8
50°	15.9
52.5°	13.1
55°	11.5
57.5°	9.8
60°	8.7
62.5°	7.7
65°	6.6
67.5°	5.5
70°	4.4
72.5°	3.8
75°	3.3
77.5°	2.7
80°	2.2
82.5°	1.6
85°	1.1
87.5°	0.5



TEST NUMBER: P1273716
CATALOG NUMBER: P3AS09R359830DE010 E3DLP1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)