

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272698

Luminaire Tested: P3AS20R409827D010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1272698
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R409827D010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R40 optic, 2700K CCT AND, 98CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 812.1 lumens
Efficiency: N/A
Efficacy: 29.6 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1272698

CATALOG NUMBER: P3AS20R409827D010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1272698

CATALOG NUMBER: P3AS20R409827D010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	112	109	107	105	105	104	102		102	100	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	104	99	94	91	102	97	93	90	95	91	88		92	89	87		90
4	100	93	88	85	98	92	88	84	90	86	83		88	85	82		86
5	96	88	83	79	94	88	83	79	86	82	78		84	81	78		83
6	92	84	79	75	91	83	78	75	82	78	74		81	77	74		79
7	88	80	75	71	87	79	74	71	78	74	71		77	73	70		76
8	85	76	71	68	84	76	71	67	75	70	67		74	70	67		73
9	82	73	68	64	81	73	68	64	72	67	64		71	67	64		70
10	78	70	65	62	78	70	65	61	69	64	61		68	64	61		67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	359313
5°	348865
10°	316583
15°	261545
20°	188666
25°	116692
30°	63174
35°	32658
40°	17748
45°	9955
50°	4981
55°	3747
60°	3377
65°	3269
70°	3142
75°	2965
80°	2652
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9955 cd/sqm

TEST NUMBER: P1272698

CATALOG NUMBER: P3AS20R409827D010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.1	18.0
10°-20°	313.7	38.6
20°-30°	223.9	27.6
30°-40°	82.4	10.1
40°-50°	26.0	3.2
50°-60°	9.0	1.1
60°-70°	6.2	0.8
70°-80°	3.7	0.5
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	683.7	84.2
0°-40°	766.1	94.3
0°-60°	801.1	98.6
0°-90°	812.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	812.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1639	
5°	1585	146
15°	1152	314
25°	482	224
35°	122	82
45°	32	26
55°	10	9
65°	6	6
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1272698

CATALOG NUMBER: P3AS20R409827D010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1638.6
2.5°	1626.0
5°	1584.9
7.5°	1516.6
10°	1421.8
12.5°	1301.2
15°	1152.1
17.5°	984.8
20°	808.5
22.5°	634.9
25°	482.3
27.5°	354.1
30°	249.5
32.5°	174.9
35°	122.0
37.5°	86.4
40°	62.0
42.5°	44.6
45°	32.1
47.5°	21.6
50°	14.6
52.5°	10.5
55°	9.8
57.5°	9.1
60°	7.7
62.5°	7.0
65°	6.3
67.5°	5.6
70°	4.9
72.5°	4.2
75°	3.5
77.5°	2.8
80°	2.1
82.5°	1.4
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)