

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273804

Luminaire Tested: P3AS09R509830DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273804
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R509830DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 98CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 404.0 lumens
Efficiency: N/A
Efficacy: 36.7 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273804

CATALOG NUMBER: P3AS09R509830DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1273804

CATALOG NUMBER: P3AS09R509830DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	85	91	87	83		88	85	82		86
4	96	88	82	78	94	87	82	78	85	80	77		83	79	76		81
5	91	83	76	72	90	82	76	72	80	75	71		78	74	70		77
6	87	77	71	67	85	77	71	67	75	70	66		74	69	66		72
7	82	73	67	62	81	72	66	62	71	66	62		70	65	61		68
8	78	69	63	58	77	68	62	58	67	62	58		66	61	58		65
9	75	65	59	55	74	64	59	55	63	58	55		63	58	54		62
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	117513
5°	114329
10°	105431
15°	92736
20°	77567
25°	61528
30°	45146
35°	31026
40°	19723
45°	11009
50°	5970
55°	5008
60°	4298
65°	3995
70°	3526
75°	3219
80°	2778
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 11009 cd/sqm

TEST NUMBER: P1273804

CATALOG NUMBER: P3AS09R509830DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.1	11.9
10°-20°	113.1	28.0
20°-30°	115.7	28.6
30°-40°	73.4	18.2
40°-50°	29.2	7.2
50°-60°	11.8	2.9
60°-70°	7.6	1.9
70°-80°	3.9	1.0
80°-90°	1.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	277.0	68.6
0°-40°	350.3	86.7
0°-60°	391.4	96.9
0°-90°	404.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	404.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	536	
5°	519	48
15°	408	113
25°	254	116
35°	116	73
45°	36	29
55°	13	12
65°	8	8
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1273804

CATALOG NUMBER: P3AS09R509830DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	535.9
2.5°	532.0
5°	519.4
7.5°	499.8
10°	473.5
12.5°	442.4
15°	408.5
17.5°	371.3
20°	332.4
22.5°	293.6
25°	254.3
27.5°	214.9
30°	178.3
32.5°	145.4
35°	115.9
37.5°	90.8
40°	68.9
42.5°	50.9
45°	35.5
47.5°	24.1
50°	17.5
52.5°	14.8
55°	13.1
57.5°	11.5
60°	9.8
62.5°	8.7
65°	7.7
67.5°	6.6
70°	5.5
72.5°	4.4
75°	3.8
77.5°	2.7
80°	2.2
82.5°	1.6
85°	1.1
87.5°	0.5
90°	0.0

(END OF REPORT)