

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273806

Luminaire Tested: P3AS09R559830DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273806
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-36)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R559830DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R55 optic, 3000K CCT AND, 98CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 727.9 lumens
Efficiency: N/A
Efficacy: 66.2 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273806

CATALOG NUMBER: P3AS09R559830DE010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1273806

CATALOG NUMBER: P3AS09R559830DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	112	109	107	105	105	104	102		101	100	99		98
2	109	104	101	98	107	103	99	96	100	97	94		97	94	92		94
3	104	98	94	90	102	97	93	89	94	91	88		92	89	86		90
4	99	92	87	84	98	91	87	83	89	85	82		87	84	81		86
5	95	87	82	78	93	86	81	78	85	80	77		83	79	76		82
6	91	83	77	73	89	82	77	73	80	76	72		79	75	72		78
7	87	78	73	69	85	78	72	69	76	72	68		75	71	68		74
8	83	74	69	65	82	74	69	65	73	68	65		72	67	64		71
9	79	71	65	61	78	70	65	61	69	64	61		68	64	61		68
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	201914
5°	200044
10°	208079
15°	205177
20°	189203
25°	153952
30°	93508
35°	32364
40°	9246
45°	4404
50°	1876
55°	841
60°	965
65°	830
70°	705
75°	932
80°	631
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4404 cd/sqm

TEST NUMBER: P1273806

CATALOG NUMBER: P3AS09R559830DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.9	12.1
10°-20°	251.2	34.5
20°-30°	280.1	38.5
30°-40°	91.6	12.6
40°-50°	12.1	1.7
50°-60°	2.6	0.4
60°-70°	1.5	0.2
70°-80°	0.9	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	619.1	85.0
0°-40°	710.7	97.6
0°-60°	725.4	99.6
0°-90°	727.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	727.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	921	
5°	909	88
15°	904	251
25°	636	280
35°	121	92
45°	14	12
55°	2	3
65°	2	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1273806

CATALOG NUMBER: P3AS09R559830DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	920.8
2.5°	914.2
5°	908.8
7.5°	921.9
10°	934.5
12.5°	927.9
15°	903.8
17.5°	865.5
20°	810.8
22.5°	735.3
25°	636.3
27.5°	510.5
30°	369.3
32.5°	226.5
35°	120.9
37.5°	61.3
40°	32.3
42.5°	20.8
45°	14.2
47.5°	9.8
50°	5.5
52.5°	3.3
55°	2.2
57.5°	2.2
60°	2.2
62.5°	1.6
65°	1.6
67.5°	1.1
70°	1.1
72.5°	1.1
75°	1.1
77.5°	0.5
80°	0.5
82.5°	0.5
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)