

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273834

Luminaire Tested: P3AS09R609830DE010 E3CB1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273834
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R609830DE010 E3CB1MB
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 98CRI , E3CB1MB TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 706.9 lumens
Efficiency: N/A
Efficacy: 64.3 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273834

CATALOG NUMBER: P3AS09R609830DE010 E3CB1MB

Luminous Intensity Polar Plot



TEST NUMBER: P1273834

CATALOG NUMBER: P3AS09R609830DE010 E3CB1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	108	106		111	109	106	104		105	103	101		101	100	98		97	96	95
2	108	103	99	96		106	102	98	95		98	95	93		95	93	91		93	91	89
3	103	96	91	88		101	95	90	87		92	89	85		90	87	84		88	85	83
4	98	90	85	81		96	89	84	80		87	83	79		85	81	78		83	80	77
5	93	84	79	74		91	84	78	74		82	77	73		80	76	73		79	75	72
6	88	79	73	69		87	79	73	69		77	72	68		76	71	68		74	70	68
7	84	75	69	64		82	74	68	64		73	68	64		71	67	64		70	66	63
8	80	70	64	60		79	70	64	60		69	64	60		68	63	60		67	63	59
9	76	66	61	57		75	66	60	56		65	60	56		64	59	56		63	59	56
10	72	63	57	53		71	62	57	53		62	56	53		61	56	53		60	56	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	168824
5°	162139
10°	166931
15°	169082
20°	149300
25°	125814
30°	102041
35°	66468
40°	30514
45°	11691
50°	3923
55°	1032
60°	965
65°	830
70°	705
75°	932
80°	631
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11691 cd/sqm

TEST NUMBER: P1273834

CATALOG NUMBER: P3AS09R609830DE010 E3CB1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.9	10.0
10°-20°	204.0	28.9
20°-30°	237.9	33.7
30°-40°	153.5	21.7
40°-50°	34.4	4.9
50°-60°	3.4	0.5
60°-70°	1.6	0.2
70°-80°	0.9	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	512.7	72.5
0°-40°	666.2	94.2
0°-60°	704.1	99.6
0°-90°	706.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	706.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	770	
5°	737	71
15°	745	204
25°	520	238
35°	248	154
45°	38	34
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1273834

CATALOG NUMBER: P3AS09R609830DE010 E3CB1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	769.9
2.5°	757.3
5°	736.6
7.5°	735.5
10°	749.7
12.5°	759.0
15°	744.8
17.5°	702.1
20°	639.8
22.5°	574.7
25°	520.0
27.5°	466.4
30°	403.0
32.5°	328.6
35°	248.3
37.5°	169.5
40°	106.6
42.5°	64.0
45°	37.7
47.5°	21.9
50°	11.5
52.5°	3.8
55°	2.7
57.5°	2.2
60°	2.2
62.5°	1.6
65°	1.6
67.5°	1.6
70°	1.1
72.5°	1.1
75°	1.1
77.5°	0.5
80°	0.5
82.5°	0.5
85°	0.5
87.5°	0.0
90°	0.0

(END OF REPORT)