

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273855

Luminaire Tested: P3AS09R609830DE010 E3DLD1WH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1273855  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R609830DE010 E3DLD1WH  
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 98CRI , E3DLD1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 451.0 lumens  
Efficiency: N/A  
Efficacy: 41.0 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1273855  
CATALOG NUMBER: P3AS09R609830DE010 E3DLD1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P1273855  
 CATALOG NUMBER: P3AS09R609830DE010 E3DLD1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91	91	91	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82	82	82	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74	74	74	74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67	67	67	67
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61	61	61	61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56	56	56	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51	51	51	51
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47	47	47	47
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44	44	44	44
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41	41	41	41

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	80059
5°	79155
10°	76418
15°	72191
20°	66552
25°	60270
30°	53502
35°	45722
40°	36354
45°	25646
50°	15317
55°	7761
60°	7456
65°	6797
70°	6347
75°	6015
80°	5556
85°	4026

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 25646 cd/sqm



TEST NUMBER: P1273855  
 CATALOG NUMBER: P3AS09R609830DE010 E3DLD1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	33.8	7.5
10°-20°	88.9	19.7
20°-30°	114.1	25.3
30°-40°	105.8	23.5
40°-50°	64.4	14.3
50°-60°	21.5	4.8
60°-70°	13.1	2.9
70°-80°	7.4	1.6
80°-90°	2.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	236.8	52.5
0°-40°	342.6	76.0
0°-60°	428.5	95.0
0°-90°	451.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	451.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	365	
5°	360	34
15°	318	89
25°	249	114
35°	171	106
45°	83	64
55°	20	21
65°	13	13
75°	7	7
85°	2	2
90°	0	



TEST NUMBER: P1273855  
CATALOG NUMBER: P3AS09R609830DE010 E3DLD1WH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	365.1
2.5°	363.5
5°	359.6
7.5°	352.5
10°	343.2
12.5°	331.7
15°	318.0
17.5°	302.2
20°	285.2
22.5°	267.1
25°	249.1
27.5°	230.4
30°	211.3
32.5°	192.1
35°	170.8
37.5°	148.3
40°	127.0
42.5°	104.5
45°	82.7
47.5°	64.0
50°	44.9
52.5°	26.8
55°	20.3
57.5°	18.6
60°	17.0
62.5°	14.8
65°	13.1
67.5°	11.5
70°	9.9
72.5°	8.2
75°	7.1
77.5°	5.5
80°	4.4
82.5°	2.7
85°	1.6
87.5°	1.1
90°	0.0

(END OF REPORT)