

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272781

Luminaire Tested: P3AS20R559827D010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1272781
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R559827D010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R55 optic, 2700K CCT AND, 98CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 760.0 lumens
Efficiency: N/A
Efficacy: 27.7 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1272781

CATALOG NUMBER: P3AS20R559827D010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1272781

CATALOG NUMBER: P3AS20R559827D010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	89	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	86	78	73	68	77	72	68		75	71	68		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	64	60	78	70	64	60	69	63	60		67	63	60		67
9	76	66	61	57	75	66	60	56	65	60	56		64	59	56		63
10	73	63	57	53	72	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	208689
5°	206581
10°	199484
15°	184405
20°	159124
25°	125669
30°	89153
35°	57474
40°	34522
45°	19444
50°	10473
55°	3747
60°	3377
65°	3269
70°	3142
75°	2965
80°	2652
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19444 cd/sqm

TEST NUMBER: P1272781

CATALOG NUMBER: P3AS20R559827D010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.3	11.6
10°-20°	224.6	29.6
20°-30°	235.4	31.0
30°-40°	137.3	18.1
40°-50°	51.4	6.8
50°-60°	12.1	1.6
60°-70°	6.2	0.8
70°-80°	3.7	0.5
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	548.3	72.1
0°-40°	685.6	90.2
0°-60°	749.1	98.6
0°-90°	760.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	760.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	952	
5°	938	88
15°	812	225
25°	519	235
35°	215	137
45°	63	51
55°	10	12
65°	6	6
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1272781

CATALOG NUMBER: P3AS20R559827D010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	951.7
2.5°	948.9
5°	938.5
7.5°	921.7
10°	895.9
12.5°	859.7
15°	812.3
17.5°	752.3
20°	681.9
22.5°	603.1
25°	519.4
27.5°	433.7
30°	352.1
32.5°	278.2
35°	214.7
37.5°	163.1
40°	120.6
42.5°	86.5
45°	62.7
47.5°	45.3
50°	30.7
52.5°	17.4
55°	9.8
57.5°	8.4
60°	7.7
62.5°	7.0
65°	6.3
67.5°	5.6
70°	4.9
72.5°	4.2
75°	3.5
77.5°	2.8
80°	2.1
82.5°	1.4
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)