

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273947

Luminaire Tested: P3AS13R159830DE010 E3PHLD1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273947
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R159830DE010 E3PHLD1MW
Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 98CRI , E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 478.0 lumens
Efficiency: N/A
Efficacy: 33.0 lumens/watt
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.66
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273947

CATALOG NUMBER: P3AS13R159830DE010 E3PHLD1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1273947

CATALOG NUMBER: P3AS13R159830DE010 E3PHLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	101	102	100	97		98	96	95		95
2	104	98	93	89	102	97	92	88	93	89	86		90	87	84		87
3	98	90	84	79	96	88	83	78	85	81	77		83	79	75		81
4	92	82	76	70	90	81	75	70	79	73	69		77	72	68		75
5	86	76	69	64	84	75	68	63	73	67	63		71	66	62		70
6	81	71	63	58	79	70	63	58	68	62	58		67	61	57		65
7	77	66	59	54	75	65	58	54	64	58	53		62	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	69	58	51	47	68	57	51	46	56	50	46		55	50	46		54
10	65	54	48	44	64	54	48	44	53	47	43		52	47	43		52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	139090
5°	130398
10°	106923
15°	83065
20°	65572
25°	52261
30°	41956
35°	34238
40°	28224
45°	23723
50°	20400
55°	17624
60°	15613
65°	13594
70°	12117
75°	9743
80°	7956
85°	5284

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 23723 cd/sqm

TEST NUMBER: P1273947

CATALOG NUMBER: P3AS13R159830DE010 E3PHLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.9	11.1
10°-20°	102.5	21.4
20°-30°	99.6	20.8
30°-40°	80.5	16.8
40°-50°	59.8	12.5
50°-60°	41.8	8.7
60°-70°	26.2	5.5
70°-80°	12.4	2.6
80°-90°	2.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	255.0	53.4
0°-40°	335.6	70.2
0°-60°	437.1	91.5
0°-90°	478.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	478.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	634	
5°	592	53
15°	366	102
25°	216	100
35°	128	81
45°	76	60
55°	46	42
65°	26	26
75°	12	12
85°	2	2
90°	0	

TEST NUMBER: P1273947

CATALOG NUMBER: P3AS13R159830DE010 E3PHLD1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	634.3
2.5°	623.9
5°	592.4
7.5°	542.1
10°	480.2
12.5°	419.4
15°	365.9
17.5°	320.8
20°	281.0
22.5°	246.4
25°	216.0
27.5°	188.7
30°	165.7
32.5°	145.7
35°	127.9
37.5°	112.2
40°	98.6
42.5°	87.0
45°	76.5
47.5°	68.2
50°	59.8
52.5°	52.4
55°	46.1
57.5°	40.9
60°	35.6
62.5°	30.4
65°	26.2
67.5°	22.0
70°	18.9
72.5°	14.7
75°	11.5
77.5°	8.4
80°	6.3
82.5°	3.1
85°	2.1
87.5°	0.0
90°	0.0

(END OF REPORT)