

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274013

Luminaire Tested: P3AS13R309830DE010 E3D1H

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274013
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R309830DE010 E3D1H
Description: 3in Adjustable LED luminaire with, R30 optic, 3000K CCT AND, 98CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 916.1 lumens
Efficiency: N/A
Efficacy: 63.2 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274013
CATALOG NUMBER: P3AS13R309830DE010 E3D1H

Luminous Intensity Polar Plot





TEST NUMBER: P1274013
 CATALOG NUMBER: P3AS13R309830DE010 E3D1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	97	97
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	94	94	94	94
3	108	103	100	97	106	102	99	96	99	97	95	97	95	93	95	93	92	90	90	90	90
4	105	99	95	92	103	98	95	92	96	93	91	94	92	90	93	91	89	88	88	88	88
5	101	96	92	89	100	95	91	88	93	90	87	92	89	87	90	88	86	85	85	85	85
6	99	92	88	85	97	92	88	85	90	87	84	89	86	84	88	85	83	82	82	82	82
7	96	89	85	82	95	89	85	82	88	84	82	87	84	81	86	83	81	80	80	80	80
8	93	87	83	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78	78	78	78
9	91	84	80	77	90	84	80	77	83	79	77	82	79	77	81	79	77	76	76	76	76
10	88	82	78	75	88	81	78	75	81	77	75	80	77	75	80	77	75	74	74	74	74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	728801
5°	719303
10°	628000
15°	399162
20°	158144
25°	52818
30°	24586
35°	11136
40°	4265
45°	2109
50°	614
55°	268
60°	175
65°	208
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2109 cd/sqm



TEST NUMBER: P1274013

CATALOG NUMBER: P3AS13R309830DE010 E3D1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	298.8	32.6
10°-20°	463.3	50.6
20°-30°	119.5	13.0
30°-40°	28.1	3.1
40°-50°	5.5	0.6
50°-60°	0.6	0.1
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	881.5	96.2
0°-40°	909.6	99.3
0°-60°	915.7	100.0
0°-90°	916.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	916.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3324	
5°	3268	299
15°	1758	463
25°	218	119
35°	42	28
45°	7	5
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1274013
CATALOG NUMBER: P3AS13R309830DE010 E3D1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	3323.6
1°	3321.1
2°	3313.3
3°	3304.4
4°	3291.2
5°	3267.8
6°	3229.7
7°	3166.4
8°	3080.0
9°	2967.3
10°	2820.4
11°	2645.9
12°	2455.3
13°	2235.9
14°	2006.2
15°	1758.3
16°	1515.5
17°	1281.5
18°	1057.1
19°	851.3
20°	677.7
21°	533.4
22°	419.6
23°	332.1
24°	266.0
25°	218.3
26°	182.1
27°	154.7
28°	133.7
29°	114.5
30°	97.1
32.5°	61.2
35°	41.6
37.5°	26.0
40°	14.9
42.5°	10.0
45°	6.8
47.5°	3.9
50°	1.8
52.5°	0.7
55°	0.7
57.5°	0.4
60°	0.4
62.5°	0.4
65°	0.4



TEST NUMBER: P1274013
CATALOG NUMBER: P3AS13R309830DE010 E3D1H

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.4
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)