

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272858

Luminaire Tested: P3AS20R709827D010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1272858
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R709827D010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R70 optic, 2700K CCT AND, 98CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1779.0 lumens
Efficiency: N/A
Efficacy: 64.9 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1272858

CATALOG NUMBER: P3AS20R709827D010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1272858

CATALOG NUMBER: P3AS20R709827D010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85
4	95	87	81	77	94	86	81	76	84	79	75		82	78	75		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	75	69	64	83	75	69	64	73	68	64		72	67	63		70
7	80	70	64	59	79	70	64	59	68	63	59		67	62	59		66
8	76	66	59	55	75	65	59	55	64	58	55		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	50		58
10	68	58	52	47	67	57	51	47	56	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	353261
5°	337089
10°	320724
15°	312147
20°	300606
25°	284508
30°	264623
35°	222292
40°	143268
45°	66581
50°	17466
55°	4358
60°	4386
65°	3684
70°	3654
75°	3643
80°	3536
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 66581 cd/sqm

TEST NUMBER: P1272858

CATALOG NUMBER: P3AS20R709827D010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	143.4	8.1
10°-20°	386.4	21.7
20°-30°	539.8	30.3
30°-40°	500.5	28.1
40°-50°	179.4	10.1
50°-60°	15.2	0.9
60°-70°	7.6	0.4
70°-80°	4.9	0.3
80°-90°	1.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1069.5	60.1
0°-40°	1570.0	88.3
0°-60°	1764.7	99.2
0°-90°	1779.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1779.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1611	
5°	1531	143
15°	1375	386
25°	1176	540
35°	830	501
45°	215	179
55°	11	15
65°	7	8
75°	4	5
85°	1	2
90°	0	

TEST NUMBER: P1272858

CATALOG NUMBER: P3AS20R709827D010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	1611.0
2.5°	1586.8
5°	1531.4
7.5°	1480.2
10°	1440.4
12.5°	1407.7
15°	1375.0
17.5°	1335.2
20°	1288.2
22.5°	1234.2
25°	1175.9
27.5°	1116.2
30°	1045.1
32.5°	954.1
35°	830.4
37.5°	672.6
40°	500.5
42.5°	341.3
45°	214.7
47.5°	119.4
50°	51.2
52.5°	17.1
55°	11.4
57.5°	10.0
60°	10.0
62.5°	8.5
65°	7.1
67.5°	7.1
70°	5.7
72.5°	5.7
75°	4.3
77.5°	4.3
80°	2.8
82.5°	2.8
85°	1.4
87.5°	1.4
90°	0.0

(END OF REPORT)