

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274018

Luminaire Tested: P3AS13R309830DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274018
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R309830DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R30 optic, 3000K CCT AND, 98CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 377.0 lumens
Efficiency: N/A
Efficacy: 26.0 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274018
CATALOG NUMBER: P3AS13R309830DE010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1274018
 CATALOG NUMBER: P3AS13R309830DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	90	90	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	86	86	86
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82	82	82	82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	78	78	78
6	94	86	81	78	92	85	81	77	84	80	77	83	79	76	81	78	76	75	75	75	75
7	90	82	77	74	89	82	77	74	81	76	73	80	76	73	78	75	73	71	71	71	71
8	87	79	74	71	86	79	74	71	78	73	70	77	73	70	76	72	70	69	69	69	69
9	84	76	71	68	83	75	71	68	75	70	67	74	70	67	73	70	67	66	66	66	66
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	63	63	63	63

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	219982
5°	209377
10°	176127
15°	127015
20°	78780
25°	44809
30°	24890
35°	13545
40°	7128
45°	3876
50°	2081
55°	1376
60°	1228
65°	1297
70°	1154
75°	932
80°	884
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3876 cd/sqm



TEST NUMBER: P1274018
 CATALOG NUMBER: P3AS13R309830DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.7	22.7
10°-20°	152.3	40.4
20°-30°	88.0	23.3
30°-40°	33.4	8.9
40°-50°	10.3	2.7
50°-60°	3.5	0.9
60°-70°	2.3	0.6
70°-80°	1.3	0.3
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	325.9	86.4
0°-40°	359.3	95.3
0°-60°	373.0	98.9
0°-90°	377.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	377.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1003	
5°	951	86
15°	560	152
25°	185	88
35°	51	33
45°	12	10
55°	4	3
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1274018
CATALOG NUMBER: P3AS13R309830DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1003.2
1°	1002.5
2°	996.5
3°	985.1
4°	970.8
5°	951.2
6°	926.3
7°	898.5
8°	867.6
9°	830.5
10°	791.0
11°	748.2
12°	703.0
13°	655.6
14°	607.6
15°	559.5
17.5°	441.3
20°	337.6
22.5°	250.4
25°	185.2
27.5°	134.6
30°	98.3
32.5°	70.9
35°	50.6
37.5°	35.3
40°	24.9
42.5°	17.5
45°	12.5
47.5°	8.5
50°	6.1
52.5°	4.3
55°	3.6
57.5°	3.2
60°	2.8
62.5°	2.5
65°	2.5
67.5°	2.1
70°	1.8
72.5°	1.4
75°	1.1
77.5°	1.1
80°	0.7
82.5°	0.7
85°	0.4
87.5°	0.0



TEST NUMBER: P1274018
CATALOG NUMBER: P3AS13R309830DE010 E3DL1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)