

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272869

Luminaire Tested: P3AS20R709827D010 E3DL1H

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1272869  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS20R709827D010 E3DL1H  
Description: 3in Adjustable LED luminaire with, R70 optic, 2700K CCT AND, 98CRI , E3DL1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1432.0 lumens  
Efficiency: N/A  
Efficacy: 52.3 lumens/watt  
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 27.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1272869

CATALOG NUMBER: P3AS20R709827D010 E3DL1H

### Luminous Intensity Polar Plot



TEST NUMBER: P1272869

CATALOG NUMBER: P3AS20R709827D010 E3DL1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 110 | 107 | 104 | 110 | 107 | 105 | 103 | 103 | 101 | 100 |  | 100 | 98  | 97  |  | 96  |
| 2   | 106 | 101 | 96  | 93  | 104 | 99  | 95  | 92  | 96  | 93  | 90  |  | 93  | 90  | 88  |  | 90  |
| 3   | 100 | 93  | 88  | 83  | 98  | 92  | 87  | 82  | 89  | 85  | 81  |  | 86  | 83  | 80  |  | 84  |
| 4   | 94  | 86  | 80  | 75  | 93  | 85  | 79  | 75  | 83  | 78  | 74  |  | 81  | 76  | 73  |  | 79  |
| 5   | 89  | 80  | 73  | 69  | 87  | 79  | 73  | 68  | 77  | 72  | 68  |  | 75  | 71  | 67  |  | 74  |
| 6   | 84  | 74  | 68  | 63  | 82  | 73  | 67  | 63  | 72  | 66  | 62  |  | 70  | 65  | 62  |  | 69  |
| 7   | 79  | 69  | 62  | 58  | 78  | 68  | 62  | 58  | 67  | 61  | 57  |  | 66  | 61  | 57  |  | 65  |
| 8   | 75  | 65  | 58  | 53  | 74  | 64  | 58  | 53  | 63  | 57  | 53  |  | 62  | 57  | 53  |  | 61  |
| 9   | 71  | 60  | 54  | 50  | 70  | 60  | 54  | 50  | 59  | 53  | 49  |  | 58  | 53  | 49  |  | 57  |
| 10  | 67  | 57  | 50  | 46  | 66  | 56  | 50  | 46  | 55  | 50  | 46  |  | 55  | 49  | 46  |  | 54  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 277215 |
| 5°  | 273893 |
| 10° | 265994 |
| 15° | 254712 |
| 20° | 238604 |
| 25° | 216763 |
| 30° | 187244 |
| 35° | 149238 |
| 40° | 108689 |
| 45° | 71449  |
| 50° | 33466  |
| 55° | 10322  |
| 60° | 9999   |
| 65° | 9599   |
| 70° | 9104   |
| 75° | 9658   |
| 80° | 8966   |
| 85° | 7045   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 71449 cd/sqm

TEST NUMBER: P1272869

CATALOG NUMBER: P3AS20R709827D010 E3DL1H

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 117.2  | 8.2       |
| 10°-20°   | 314.0  | 21.9      |
| 20°-30°   | 408.1  | 28.5      |
| 30°-40°   | 346.3  | 24.2      |
| 40°-50°   | 178.6  | 12.5      |
| 50°-60°   | 34.4   | 2.4       |
| 60°-70°   | 18.7   | 1.3       |
| 70°-80°   | 11.4   | 0.8       |
| 80°-90°   | 3.3    | 0.2       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 839.3  | 58.6      |
| 0°-40°    | 1185.6 | 82.8      |
| 0°-60°    | 1398.6 | 97.7      |
| 0°-90°    | 1432.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1432.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1264 |      |
| 5°  | 1244 | 117  |
| 15° | 1122 | 314  |
| 25° | 896  | 408  |
| 35° | 558  | 346  |
| 45° | 230  | 179  |
| 55° | 27   | 34   |
| 65° | 18   | 19   |
| 75° | 11   | 11   |
| 85° | 3    | 3    |
| 90° | 0    |      |

TEST NUMBER: P1272869

CATALOG NUMBER: P3AS20R709827D010 E3DL1H

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1264.2 |
| 2.5°  | 1260.0 |
| 5°    | 1244.3 |
| 7.5°  | 1221.6 |
| 10°   | 1194.6 |
| 12.5° | 1160.4 |
| 15°   | 1122.0 |
| 17.5° | 1075.1 |
| 20°   | 1022.5 |
| 22.5° | 962.8  |
| 25°   | 895.9  |
| 27.5° | 820.5  |
| 30°   | 739.5  |
| 32.5° | 649.9  |
| 35°   | 557.5  |
| 37.5° | 466.4  |
| 40°   | 379.7  |
| 42.5° | 298.6  |
| 45°   | 230.4  |
| 47.5° | 169.2  |
| 50°   | 98.1   |
| 52.5° | 42.7   |
| 55°   | 27.0   |
| 57.5° | 25.6   |
| 60°   | 22.8   |
| 62.5° | 21.3   |
| 65°   | 18.5   |
| 67.5° | 17.1   |
| 70°   | 14.2   |
| 72.5° | 12.8   |
| 75°   | 11.4   |
| 77.5° | 8.5    |
| 80°   | 7.1    |
| 82.5° | 4.3    |
| 85°   | 2.8    |
| 87.5° | 1.4    |
| 90°   | 0.0    |

(END OF REPORT)