

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272897

Luminaire Tested: P3AS02R159830DE010 E3DL1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1272897
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R159830DE010 E3DL1WH
Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 98CRI , E3DL1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 110.0 lumens
Efficiency: N/A
Efficacy: 30.6 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1272897
CATALOG NUMBER: P3AS02R159830DE010 E3DL1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1272897

CATALOG NUMBER: P3AS02R159830DE010 E3DL1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	106	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93	93
2	108	103	98	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86	86	86	86
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80	80	80	80
4	97	90	84	80	95	88	83	79	86	82	78	84	81	77	82	79	77	75	75	75	75
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70	70	70	70
6	88	79	73	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66	66	66	66
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62	62	62	62
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59	59	59	59
9	77	68	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	56	56	56	56
10	74	64	59	55	73	64	59	55	63	58	55	62	58	55	62	57	54	53	53	53	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	47430
5°	43848
10°	35003
15°	26447
20°	20138
25°	15340
30°	10989
35°	7174
40°	4408
45°	2667
50°	1774
55°	1376
60°	1184
65°	1038
70°	898
75°	932
80°	631
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2667 cd/sqm



TEST NUMBER: P1272897
 CATALOG NUMBER: P3AS02R159830DE010 E3DL1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	17.6	16.0
10°-20°	32.6	29.6
20°-30°	29.0	26.3
30°-40°	17.2	15.6
40°-50°	7.0	6.4
50°-60°	3.3	3.0
60°-70°	2.0	1.8
70°-80°	1.1	1.0
80°-90°	0.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	79.2	72.0
0°-40°	96.3	87.5
0°-60°	106.7	96.9
0°-90°	110.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	110.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	216	
5°	199	18
15°	116	33
25°	63	29
35°	27	17
45°	9	7
55°	4	3
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1272897
CATALOG NUMBER: P3AS02R159830DE010 E3DL1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	216.3
1°	215.8
2°	214.2
3°	211.0
4°	205.6
5°	199.2
6°	192.2
7°	184.0
8°	175.4
9°	166.7
10°	157.2
12.5°	135.6
15°	116.5
17.5°	100.0
20°	86.3
22.5°	74.1
25°	63.4
27.5°	53.1
30°	43.4
32.5°	34.7
35°	26.8
37.5°	20.5
40°	15.4
42.5°	11.4
45°	8.6
47.5°	6.6
50°	5.2
52.5°	4.3
55°	3.6
57.5°	3.0
60°	2.7
62.5°	2.3
65°	2.0
67.5°	1.8
70°	1.4
72.5°	1.3
75°	1.1
77.5°	0.7
80°	0.5
82.5°	0.4
85°	0.2
87.5°	0.2
90°	0.0

(END OF REPORT)