

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274046

Luminaire Tested: P3AS13R359830DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274046
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R359830DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R35 optic, 3000K CCT AND, 98CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 374.0 lumens
Efficiency: N/A
Efficacy: 25.8 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274046
CATALOG NUMBER: P3AS13R359830DE010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1274046

CATALOG NUMBER: P3AS13R359830DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	90	90	90	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85	85	85	85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80	80	80	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76	76	76	76
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73	73	73	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	70	70	70	70
8	85	77	72	69	84	77	72	68	76	71	68	75	71	68	74	70	68	66	66	66	66
9	82	74	69	66	81	74	69	65	73	68	65	72	68	65	71	67	65	64	64	64	64
10	79	71	66	63	78	71	66	63	70	66	63	69	65	62	69	65	62	61	61	61	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	188625
5°	181289
10°	157957
15°	120977
20°	80950
25°	48971
30°	28106
35°	15714
40°	8359
45°	4311
50°	2047
55°	1644
60°	1579
65°	1297
70°	1346
75°	1186
80°	1389
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4311 cd/sqm



TEST NUMBER: P1274046
 CATALOG NUMBER: P3AS13R359830DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.9	20.0
10°-20°	145.2	38.8
20°-30°	95.1	25.4
30°-40°	38.6	10.3
40°-50°	11.6	3.1
50°-60°	3.9	1.1
60°-70°	2.6	0.7
70°-80°	1.6	0.4
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	315.2	84.3
0°-40°	353.8	94.6
0°-60°	369.3	98.7
0°-90°	374.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	374.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	860	
5°	824	75
15°	533	145
25°	202	95
35°	59	39
45°	14	12
55°	4	4
65°	2	3
75°	1	2
85°	0	1
90°	0	



TEST NUMBER: P1274046
CATALOG NUMBER: P3AS13R359830DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	860.2
1°	858.8
2°	854.9
3°	847.1
4°	837.8
5°	823.6
6°	805.8
7°	785.9
8°	763.5
9°	737.8
10°	709.4
11°	677.7
12°	644.6
13°	607.6
14°	572.4
15°	532.9
17.5°	437.2
20°	346.9
22.5°	266.8
25°	202.4
27.5°	150.8
30°	111.0
32.5°	81.5
35°	58.7
37.5°	41.6
40°	29.2
42.5°	20.3
45°	13.9
47.5°	9.2
50°	6.0
52.5°	4.6
55°	4.3
57.5°	3.9
60°	3.6
62.5°	3.2
65°	2.5
67.5°	2.1
70°	2.1
72.5°	1.8
75°	1.4
77.5°	1.1
80°	1.1
82.5°	0.7
85°	0.4
87.5°	0.4



TEST NUMBER: P1274046
CATALOG NUMBER: P3AS13R359830DE010 E3DL1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)