

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274084

Luminaire Tested: P3AS13R409830DE010 E3DLD1GPH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1274084  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R409830DE010 E3DLD1GPH  
Description: 3in Adjustable LED luminaire with, R40 optic, 3000K CCT AND, 98CRI , E3DLD1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 318.0 lumens  
Efficiency: N/A  
Efficacy: 21.9 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1274084  
CATALOG NUMBER: P3AS13R409830DE010 E3DLD1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1274084  
 CATALOG NUMBER: P3AS13R409830DE010 E3DLD1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91				91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83				83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76				76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69				69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64				64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59				59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55				55
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51				51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48				48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45				45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	71376
5°	70086
10°	66064
15°	60000
20°	52715
25°	45027
30°	37297
35°	28750
40°	20467
45°	13800
50°	7539
55°	5314
60°	5000
65°	4618
70°	4103
75°	3897
80°	3157
85°	2768

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 13800 cd/sqm



TEST NUMBER: P1274084  
 CATALOG NUMBER: P3AS13R409830DE010 E3DLD1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	29.7	9.3
10°-20°	73.6	23.2
20°-30°	85.1	26.8
30°-40°	67.1	21.1
40°-50°	34.4	10.8
50°-60°	13.2	4.1
60°-70°	8.7	2.7
70°-80°	4.7	1.5
80°-90°	1.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	188.4	59.3
0°-40°	255.5	80.3
0°-60°	303.2	95.3
0°-90°	318.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	318.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	326	
5°	318	30
15°	264	74
25°	186	85
35°	107	67
45°	44	34
55°	14	13
65°	9	9
75°	5	5
85°	1	1
90°	0	



TEST NUMBER: P1274084  
CATALOG NUMBER: P3AS13R409830DE010 E3DLD1GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	325.5
2.5°	323.8
5°	318.4
7.5°	309.2
10°	296.7
12.5°	282.1
15°	264.3
17.5°	245.8
20°	225.9
22.5°	205.6
25°	186.1
27.5°	166.5
30°	147.3
32.5°	127.7
35°	107.4
37.5°	88.6
40°	71.5
42.5°	56.9
45°	44.5
47.5°	32.4
50°	22.1
52.5°	16.0
55°	13.9
57.5°	12.5
60°	11.4
62.5°	10.0
65°	8.9
67.5°	7.5
70°	6.4
72.5°	5.3
75°	4.6
77.5°	3.6
80°	2.5
82.5°	2.1
85°	1.1
87.5°	0.7
90°	0.0

(END OF REPORT)