

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274086

Luminaire Tested: P3AS13R409830DE010 E3DLD1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274086
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R409830DE010 E3DLD1LI
Description: 3in Adjustable LED luminaire with, R40 optic, 3000K CCT AND, 98CRI , E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 647.9 lumens
Efficiency: N/A
Efficacy: 44.7 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274086

CATALOG NUMBER: P3AS13R409830DE010 E3DLD1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1274086

CATALOG NUMBER: P3AS13R409830DE010 E3DLD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96
2	106	100	96	92	104	98	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	75	72		78
5	89	79	73	68	87	78	72	67	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	61		70	65	61		68
7	79	69	62	57	78	68	62	57	67	61	57		65	60	57		64
8	75	64	58	53	74	64	58	53	63	57	53		62	56	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	51	46	66	56	50	46	56	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	145471
5°	142835
10°	134622
15°	122294
20°	107436
25°	91747
30°	75986
35°	58598
40°	41707
45°	28096
50°	15317
55°	10819
60°	10175
65°	9391
70°	8335
75°	7964
80°	6440
85°	5535

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 28096 cd/sqm

TEST NUMBER: P1274086

CATALOG NUMBER: P3AS13R409830DE010 E3DLD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.5	9.3
10°-20°	150.1	23.2
20°-30°	173.5	26.8
30°-40°	136.7	21.1
40°-50°	70.2	10.8
50°-60°	26.8	4.1
60°-70°	17.7	2.7
70°-80°	9.6	1.5
80°-90°	2.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	384.0	59.3
0°-40°	520.7	80.4
0°-60°	617.7	95.3
0°-90°	647.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	647.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	663	
5°	649	61
15°	539	150
25°	379	173
35°	219	137
45°	91	70
55°	28	27
65°	18	18
75°	9	10
85°	2	3
90°	0	

TEST NUMBER: P1274086

CATALOG NUMBER: P3AS13R409830DE010 E3DLD1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	663.4
2.5°	659.7
5°	648.9
7.5°	630.0
10°	604.6
12.5°	574.9
15°	538.7
17.5°	501.0
20°	460.4
22.5°	419.0
25°	379.2
27.5°	339.3
30°	300.1
32.5°	260.3
35°	218.9
37.5°	180.5
40°	145.7
42.5°	116.0
45°	90.6
47.5°	66.0
50°	44.9
52.5°	32.6
55°	28.3
57.5°	25.4
60°	23.2
62.5°	20.3
65°	18.1
67.5°	15.2
70°	13.0
72.5°	10.9
75°	9.4
77.5°	7.2
80°	5.1
82.5°	4.3
85°	2.2
87.5°	1.4
90°	0.0

(END OF REPORT)