

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272933

Luminaire Tested: P3AS02R209830DE010 E3DLD1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1272933
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R209830DE010 E3DLD1MW
Description: 3in Adjustable LED luminaire with, R20 optic, 3000K CCT AND, 98CRI , E3DLD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 141.0 lumens
Efficiency: N/A
Efficacy: 39.2 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1272933

CATALOG NUMBER: P3AS02R209830DE010 E3DLD1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1272933

CATALOG NUMBER: P3AS02R209830DE010 E3DLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91		
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	90	87	85	83		
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76		
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70		
5	89	80	73	68	87	79	73	68	77	71	67	75	70	67	73	69	66	64		
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60		
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	60	57	55		
8	75	65	59	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52		
9	72	61	55	50	70	61	55	50	60	54	50	59	54	50	58	53	50	48		
10	68	58	51	47	67	57	51	47	56	51	47	56	50	47	55	50	47	45		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	34866
5°	33942
10°	31217
15°	27492
20°	23569
25°	19816
30°	16002
35°	12180
40°	8673
45°	5706
50°	3548
55°	2332
60°	2105
65°	1972
70°	1859
75°	1694
80°	1642
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5706 cd/sqm

TEST NUMBER: P1272933

CATALOG NUMBER: P3AS02R209830DE010 E3DLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	14.3	10.1
10°-20°	33.7	23.9
20°-30°	37.4	26.5
30°-40°	28.5	20.2
40°-50°	14.6	10.4
50°-60°	6.0	4.3
60°-70°	3.7	2.7
70°-80°	2.1	1.5
80°-90°	0.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	85.4	60.5
0°-40°	113.9	80.8
0°-60°	134.6	95.4
0°-90°	141.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	141.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	159	
5°	154	14
15°	121	34
25°	82	37
35°	46	29
45°	18	15
55°	6	6
65°	4	4
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1272933

CATALOG NUMBER: P3AS02R209830DE010 E3DLD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	159.0
1°	159.2
2°	158.5
3°	157.6
4°	156.2
5°	154.2
6°	151.9
7°	149.4
8°	146.7
9°	143.5
10°	140.2
12.5°	130.9
15°	121.1
17.5°	111.0
20°	101.0
22.5°	91.0
25°	81.9
27.5°	72.7
30°	63.2
32.5°	54.3
35°	45.5
37.5°	37.8
40°	30.3
42.5°	23.8
45°	18.4
47.5°	14.0
50°	10.4
52.5°	7.7
55°	6.1
57.5°	5.6
60°	4.8
62.5°	4.3
65°	3.8
67.5°	3.2
70°	2.9
72.5°	2.3
75°	2.0
77.5°	1.6
80°	1.3
82.5°	0.9
85°	0.5
87.5°	0.2
90°	0.0

(END OF REPORT)