

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272941

Luminaire Tested: P3AS02R259830DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1272941
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R259830DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R25 optic, 3000K CCT AND, 98CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 228.1 lumens
Efficiency: N/A
Efficacy: 63.4 lumens/watt
Spacing Criteria (0/90/45): 0.45 / 0.45 / 0.41
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1272941

CATALOG NUMBER: P3AS02R259830DE010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1272941

CATALOG NUMBER: P3AS02R259830DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99
1	115	113	111	110	113	111	109	108	107	106	105	103	103	102	100	99	99	97	96	96
2	112	108	105	103	110	107	104	102	104	101	100	101	99	98	98	97	96	94	93	93
3	108	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92	91	91
4	105	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89	88	88
5	103	97	93	90	101	96	93	90	95	92	89	93	91	89	92	90	88	87	86	86
6	100	94	90	87	99	93	90	87	92	89	87	91	88	86	90	87	86	85	84	84
7	97	91	88	85	96	91	87	85	90	87	84	89	86	84	88	85	83	82	81	81
8	95	89	85	82	94	88	85	82	88	84	82	87	84	82	86	83	81	80	79	79
9	93	87	83	80	92	86	83	80	86	82	80	85	82	80	84	81	80	79	78	78
10	91	85	81	78	90	84	81	78	84	80	78	83	80	78	82	80	78	77	76	76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	243774
5°	226083
10°	175325
15°	87923
20°	28889
25°	11493
30°	4304
35°	1258
40°	573
45°	217
50°	171
55°	153
60°	175
65°	208
70°	128
75°	169
80°	253
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 80°

Luminance: 253 cd/sqm

TEST NUMBER: P1272941

CATALOG NUMBER: P3AS02R259830DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.3	39.6
10°-20°	107.8	47.3
20°-30°	24.3	10.7
30°-40°	3.9	1.7
40°-50°	0.7	0.3
50°-60°	0.4	0.2
60°-70°	0.4	0.2
70°-80°	0.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	222.4	97.5
0°-40°	226.4	99.2
0°-60°	227.5	99.7
0°-90°	228.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	228.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1112	
5°	1027	90
15°	387	108
25°	48	24
35°	5	4
45°	1	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1272941

CATALOG NUMBER: P3AS02R259830DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	1111.7
1°	1109.9
2°	1100.9
3°	1084.4
4°	1059.5
5°	1027.1
6°	988.4
7°	946.5
8°	898.5
9°	846.0
10°	787.4
11°	719.9
12°	642.2
13°	560.8
14°	473.6
15°	387.3
17.5°	220.7
20°	123.8
22.5°	74.7
25°	47.5
27.5°	29.2
30°	17.0
32.5°	9.0
35°	4.7
37.5°	3.0
40°	2.0
42.5°	1.3
45°	0.7
47.5°	0.5
50°	0.5
52.5°	0.5
55°	0.4
57.5°	0.4
60°	0.4
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.2
72.5°	0.2
75°	0.2
77.5°	0.2
80°	0.2
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1272941

CATALOG NUMBER: P3AS02R259830DE010 E3CB1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)