

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272957

Luminaire Tested: P3AS02R259830DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1272957
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R259830DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R25 optic, 3000K CCT AND, 98CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 70.0 lumens
Efficiency: N/A
Efficacy: 19.5 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1272957

CATALOG NUMBER: P3AS02R259830DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1272957

CATALOG NUMBER: P3AS02R259830DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	16643
5°	16245
10°	15052
15°	13394
20°	11528
25°	9799
30°	8052
35°	6291
40°	4523
45°	2853
50°	1706
55°	1185
60°	1053
65°	986
70°	898
75°	847
80°	758
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2853 cd/sqm

TEST NUMBER: P1272957

CATALOG NUMBER: P3AS02R259830DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	6.8	9.8
10°-20°	16.4	23.4
20°-30°	18.5	26.5
30°-40°	14.6	20.9
40°-50°	7.4	10.6
50°-60°	3.0	4.2
60°-70°	1.9	2.7
70°-80°	1.1	1.5
80°-90°	0.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	41.8	59.6
0°-40°	56.4	80.5
0°-60°	66.8	95.3
0°-90°	70.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	70.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	76	
5°	74	7
15°	59	16
25°	40	19
35°	24	15
45°	9	7
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1272957

CATALOG NUMBER: P3AS02R259830DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	75.9
1°	75.9
2°	75.6
3°	75.2
4°	74.6
5°	73.8
6°	72.8
7°	71.7
8°	70.5
9°	69.1
10°	67.6
11°	65.9
12°	64.4
13°	62.5
14°	60.8
15°	59.0
17.5°	54.2
20°	49.4
22.5°	44.8
25°	40.5
27.5°	36.2
30°	31.8
32.5°	27.7
35°	23.5
37.5°	19.5
40°	15.8
42.5°	12.3
45°	9.2
47.5°	6.9
50°	5.0
52.5°	3.7
55°	3.1
57.5°	2.8
60°	2.4
62.5°	2.2
65°	1.9
67.5°	1.7
70°	1.4
72.5°	1.2
75°	1.0
77.5°	0.8
80°	0.6
82.5°	0.4
85°	0.3
87.5°	0.1



TEST NUMBER: P1272957

CATALOG NUMBER: P3AS02R259830DE010 E3DLD1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)