

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274196

Luminaire Tested: P3AS13R609830DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274196
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R609830DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 98CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 293.0 lumens
Efficiency: N/A
Efficacy: 20.2 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274196

CATALOG NUMBER: P3AS13R609830DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1274196

CATALOG NUMBER: P3AS13R609830DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	52013
5°	51420
10°	49654
15°	46902
20°	43240
25°	39147
30°	34765
35°	29714
40°	23616
45°	16653
50°	9961
55°	5046
60°	4824
65°	4410
70°	4103
75°	3897
80°	3536
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16653 cd/sqm

TEST NUMBER: P1274196

CATALOG NUMBER: P3AS13R609830DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	22.0	7.5
10°-20°	57.7	19.7
20°-30°	74.1	25.3
30°-40°	68.8	23.5
40°-50°	41.8	14.3
50°-60°	14.0	4.8
60°-70°	8.5	2.9
70°-80°	4.8	1.6
80°-90°	1.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	153.8	52.5
0°-40°	222.6	76.0
0°-60°	278.4	95.0
0°-90°	293.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	293.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	237	
5°	234	22
15°	207	58
25°	162	74
35°	111	69
45°	54	42
55°	13	14
65°	8	8
75°	5	5
85°	1	1
90°	0	

TEST NUMBER: P1274196

CATALOG NUMBER: P3AS13R609830DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	237.2
2.5°	236.1
5°	233.6
7.5°	229.0
10°	223.0
12.5°	215.5
15°	206.6
17.5°	196.3
20°	185.3
22.5°	173.5
25°	161.8
27.5°	149.7
30°	137.3
32.5°	124.8
35°	111.0
37.5°	96.4
40°	82.5
42.5°	67.9
45°	53.7
47.5°	41.6
50°	29.2
52.5°	17.4
55°	13.2
57.5°	12.1
60°	11.0
62.5°	9.6
65°	8.5
67.5°	7.5
70°	6.4
72.5°	5.3
75°	4.6
77.5°	3.6
80°	2.8
82.5°	1.8
85°	1.1
87.5°	0.7
90°	0.0

(END OF REPORT)