

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274201

Luminaire Tested: P3AS13R609830DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274201
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R609830DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 98CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 598.0 lumens
Efficiency: N/A
Efficacy: 41.2 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274201

CATALOG NUMBER: P3AS13R609830DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1274201

CATALOG NUMBER: P3AS13R609830DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	106154
5°	104952
10°	101334
15°	95733
20°	88231
25°	79892
30°	70948
35°	60606
40°	48205
45°	33988
50°	20298
55°	10284
60°	9868
65°	9028
70°	8399
75°	7964
80°	7324
85°	5535

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 33988 cd/sqm

TEST NUMBER: P1274201

CATALOG NUMBER: P3AS13R609830DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.8	7.5
10°-20°	117.8	19.7
20°-30°	151.3	25.3
30°-40°	140.3	23.5
40°-50°	85.4	14.3
50°-60°	28.5	4.8
60°-70°	17.3	2.9
70°-80°	9.8	1.6
80°-90°	2.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	314.0	52.5
0°-40°	454.3	76.0
0°-60°	568.2	95.0
0°-90°	598.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	598.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	484	
5°	477	45
15°	422	118
25°	330	151
35°	226	140
45°	110	85
55°	27	28
65°	17	17
75°	9	10
85°	2	3
90°	0	

TEST NUMBER: P1274201

CATALOG NUMBER: P3AS13R609830DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	484.1
2.5°	481.9
5°	476.8
7.5°	467.4
10°	455.1
12.5°	439.8
15°	421.7
17.5°	400.6
20°	378.1
22.5°	354.2
25°	330.2
27.5°	305.6
30°	280.2
32.5°	254.8
35°	226.4
37.5°	196.7
40°	168.4
42.5°	138.6
45°	109.6
47.5°	84.9
50°	59.5
52.5°	35.6
55°	26.9
57.5°	24.7
60°	22.5
62.5°	19.6
65°	17.4
67.5°	15.2
70°	13.1
72.5°	10.9
75°	9.4
77.5°	7.3
80°	5.8
82.5°	3.6
85°	2.2
87.5°	1.5
90°	0.0

(END OF REPORT)