

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273074

Luminaire Tested: P3AS02R459830DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273074
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R459830DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R45 optic, 3000K CCT AND, 98CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 76.0 lumens
Efficiency: N/A
Efficacy: 21.1 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273074

CATALOG NUMBER: P3AS02R459830DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1273074

CATALOG NUMBER: P3AS02R459830DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	92	86	82	97	90	85	81	88	83	80		85	81	78		83
4	94	85	78	74	92	84	78	73	81	76	72		79	75	71		77
5	88	79	72	67	86	78	71	67	76	70	66		74	69	65		72
6	83	73	66	61	81	72	66	61	71	65	61		69	64	60		68
7	78	68	61	57	77	67	61	56	66	60	56		65	60	56		64
8	74	64	57	52	73	63	57	52	62	56	52		61	56	52		60
9	70	60	53	49	69	59	53	49	58	52	48		57	52	48		56
10	67	56	50	45	66	56	49	45	55	49	45		54	49	45		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	16117
5°	15827
10°	14985
15°	13666
20°	12088
25°	10501
30°	9014
35°	7495
40°	5582
45°	3411
50°	1569
55°	1223
60°	1184
65°	1090
70°	1026
75°	932
80°	884
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3411 cd/sqm

TEST NUMBER: P1273074

CATALOG NUMBER: P3AS02R459830DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	6.7	8.8
10°-20°	16.8	22.1
20°-30°	19.9	26.2
30°-40°	17.3	22.8
40°-50°	8.7	11.4
50°-60°	3.0	4.0
60°-70°	2.1	2.8
70°-80°	1.2	1.5
80°-90°	0.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	43.4	57.1
0°-40°	60.7	79.8
0°-60°	72.3	95.2
0°-90°	76.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	76.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	74	
5°	72	7
15°	60	17
25°	43	20
35°	28	17
45°	11	9
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1273074

CATALOG NUMBER: P3AS02R459830DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	73.5
2.5°	73.1
5°	71.9
7.5°	70.0
10°	67.3
12.5°	63.9
15°	60.2
17.5°	56.0
20°	51.8
22.5°	47.5
25°	43.4
27.5°	39.4
30°	35.6
32.5°	31.9
35°	28.0
37.5°	23.9
40°	19.5
42.5°	15.2
45°	11.0
47.5°	7.3
50°	4.6
52.5°	3.6
55°	3.2
57.5°	3.0
60°	2.7
62.5°	2.5
65°	2.1
67.5°	1.8
70°	1.6
72.5°	1.3
75°	1.1
77.5°	0.9
80°	0.7
82.5°	0.5
85°	0.3
87.5°	0.2
90°	0.0

(END OF REPORT)