

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274249

Luminaire Tested: P3AS13R709830DE010 E3DL1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274249
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R709830DE010 E3DL1H
Description: 3in Adjustable LED luminaire with, R70 optic, 3000K CCT AND, 98CRI , E3DL1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 731.0 lumens
Efficiency: N/A
Efficacy: 50.4 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274249

CATALOG NUMBER: P3AS13R709830DE010 E3DL1H

Luminous Intensity Polar Plot





TEST NUMBER: P1274249

CATALOG NUMBER: P3AS13R709830DE010 E3DL1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	96	93	104	99	95	92	96	92	90		93	90	88		90
3	100	93	88	83	98	92	87	82	89	85	81		86	83	80		84
4	94	86	80	75	93	85	79	75	83	78	74		81	76	73		79
5	89	80	73	69	87	79	73	68	77	72	68		75	71	67		74
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	53	74	64	58	53	63	57	53		62	57	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	50	46	66	56	50	46	55	50	46		55	49	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	141524
5°	139819
10°	135780
15°	130035
20°	121811
25°	110643
30°	95584
35°	76185
40°	55475
45°	36469
50°	17091
55°	5276
60°	5087
65°	4877
70°	4680
75°	4914
80°	4546
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 36469 cd/sqm

TEST NUMBER: P1274249

CATALOG NUMBER: P3AS13R709830DE010 E3DL1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.8	8.2
10°-20°	160.3	21.9
20°-30°	208.3	28.5
30°-40°	176.8	24.2
40°-50°	91.1	12.5
50°-60°	17.6	2.4
60°-70°	9.5	1.3
70°-80°	5.8	0.8
80°-90°	1.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	428.5	58.6
0°-40°	605.3	82.8
0°-60°	714.0	97.7
0°-90°	731.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	731.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	645	
5°	635	60
15°	573	160
25°	457	208
35°	285	177
45°	118	91
55°	14	18
65°	9	10
75°	6	6
85°	2	2
90°	0	

TEST NUMBER: P1274249

CATALOG NUMBER: P3AS13R709830DE010 E3DL1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	645.4
2.5°	643.2
5°	635.2
7.5°	623.6
10°	609.8
12.5°	592.4
15°	572.8
17.5°	548.8
20°	522.0
22.5°	491.5
25°	457.3
27.5°	418.9
30°	377.5
32.5°	331.8
35°	284.6
37.5°	238.1
40°	193.8
42.5°	152.4
45°	117.6
47.5°	86.4
50°	50.1
52.5°	21.8
55°	13.8
57.5°	13.1
60°	11.6
62.5°	10.9
65°	9.4
67.5°	8.7
70°	7.3
72.5°	6.5
75°	5.8
77.5°	4.4
80°	3.6
82.5°	2.2
85°	1.5
87.5°	0.7
90°	0.0

(END OF REPORT)