

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273079

Luminaire Tested: P3AS02R459830DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273079
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R459830DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R45 optic, 3000K CCT AND, 98CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 155.0 lumens
Efficiency: N/A
Efficacy: 43.1 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273079
CATALOG NUMBER: P3AS02R459830DE010 E3DLD1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1273079

CATALOG NUMBER: P3AS02R459830DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91				91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83				83
3	99	92	86	82	97	90	85	81	88	83	80	85	81	78	83	80	77	75				75
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69				69
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63				63
6	83	73	66	61	81	72	66	61	71	65	61	69	64	60	68	63	60	58				58
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	64	59	55	54				54
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	52	50				50
9	70	60	53	49	69	59	53	49	58	52	48	57	52	48	56	52	48	47				47
10	67	56	50	45	66	56	49	45	55	49	45	54	49	45	53	48	45	44				44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	32870
5°	32291
10°	30549
15°	27855
20°	24642
25°	21388
30°	18357
35°	15312
40°	11393
45°	6977
50°	3241
55°	2523
60°	2412
65°	2231
70°	2052
75°	1949
80°	1768
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6977 cd/sqm



TEST NUMBER: P1273079

CATALOG NUMBER: P3AS02R459830DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	13.7	8.8
10°-20°	34.2	22.0
20°-30°	40.6	26.2
30°-40°	35.3	22.8
40°-50°	17.7	11.4
50°-60°	6.1	4.0
60°-70°	4.3	2.8
70°-80°	2.4	1.5
80°-90°	0.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	88.5	57.1
0°-40°	123.7	79.8
0°-60°	147.6	95.2
0°-90°	155.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	155.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	150	
5°	147	14
15°	123	34
25°	88	41
35°	57	35
45°	22	18
55°	7	6
65°	4	4
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1273079

CATALOG NUMBER: P3AS02R459830DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	149.9
2.5°	149.2
5°	146.7
7.5°	142.7
10°	137.2
12.5°	130.4
15°	122.7
17.5°	114.1
20°	105.6
22.5°	96.8
25°	88.4
27.5°	80.4
30°	72.5
32.5°	65.0
35°	57.2
37.5°	48.8
40°	39.8
42.5°	31.1
45°	22.5
47.5°	14.8
50°	9.5
52.5°	7.3
55°	6.6
57.5°	6.1
60°	5.5
62.5°	5.0
65°	4.3
67.5°	3.8
70°	3.2
72.5°	2.7
75°	2.3
77.5°	1.8
80°	1.4
82.5°	1.1
85°	0.5
87.5°	0.4
90°	0.0

(END OF REPORT)