

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273095

Luminaire Tested: P3AS02R509830DE010 E3D1WH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273095
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R509830DE010 E3D1WH
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 98CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 248.0 lumens
Efficiency: N/A
Efficacy: 68.9 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273095
CATALOG NUMBER: P3AS02R509830DE010 E3D1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1273095
 CATALOG NUMBER: P3AS02R509830DE010 E3D1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	109	107	112	110	108	106	105	104	102	102	101	99	98	97	97	97	97	97	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	94	93	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	91	88	86	85
4	100	94	89	85	99	92	88	85	90	87	84	88	85	83	87	84	82	87	84	82	80
5	96	89	84	80	94	88	83	79	86	82	79	84	81	78	83	80	77	83	80	77	76
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	79	76	73	72
7	88	80	75	71	87	79	74	71	78	74	70	77	73	70	76	72	70	76	72	70	68
8	84	76	71	67	83	76	71	67	74	70	67	74	69	66	73	69	66	73	69	66	65
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	70	66	63	62
10	78	69	64	61	77	69	64	61	68	64	60	67	63	60	67	63	60	67	63	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	86660
5°	84349
10°	80493
15°	72872
20°	63052
25°	51729
30°	29701
35°	9235
40°	2490
45°	868
50°	205
55°	76
60°	44
65°	52
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 868 cd/sqm



TEST NUMBER: P1273095
 CATALOG NUMBER: P3AS02R509830DE010 E3D1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.9	14.5
10°-20°	88.9	35.9
20°-30°	93.5	37.7
30°-40°	26.8	10.8
40°-50°	2.6	1.1
50°-60°	0.2	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	218.3	88.0
0°-40°	245.1	98.8
0°-60°	247.9	100.0
0°-90°	248.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	248.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	395	
5°	383	36
15°	321	89
25°	214	93
35°	34	27
45°	3	3
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1273095
CATALOG NUMBER: P3AS02R509830DE010 E3D1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	395.2
1°	394.6
2°	392.9
3°	390.3
4°	386.9
5°	383.2
6°	379.3
7°	375.1
8°	371.2
9°	366.6
10°	361.5
11°	355.7
12°	348.9
13°	340.5
14°	331.4
15°	321.0
16°	310.0
17°	299.3
18°	288.4
19°	278.8
20°	270.2
21°	262.0
22°	252.6
23°	241.8
24°	229.2
25°	213.8
26°	197.0
27°	178.2
28°	159.6
29°	139.5
30°	117.3
31°	96.6
32°	77.5
32.5°	69.2
33°	60.8
34°	46.6
35°	34.5
36°	25.3
37°	18.8
37.5°	16.3
38°	14.1
39°	10.9
40°	8.7
42.5°	4.9
45°	2.8



TEST NUMBER: P1273095
CATALOG NUMBER: P3AS02R509830DE010 E3D1WH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	1.6
50°	0.6
52.5°	0.3
55°	0.2
57.5°	0.2
60°	0.1
62.5°	0.1
65°	0.1
67.5°	0.1
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)