

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274282

Luminaire Tested: P3AS17R159830DE010 E3DLD1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274282
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R159830DE010 E3DLD1MW
Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 98CRI , E3DLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 928.0 lumens
Efficiency: N/A
Efficacy: 45.5 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274282
CATALOG NUMBER: P3AS17R159830DE010 E3DLD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1274282
 CATALOG NUMBER: P3AS17R159830DE010 E3DLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91			91
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83			83
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76			76
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70			70
5	89	80	73	68	87	79	73	68	77	72	67	75	71	67	74	69	66	65			65
6	84	74	68	63	83	73	67	63	72	66	62	70	66	62	69	65	61	60			60
7	80	69	63	58	78	69	63	58	67	62	58	66	61	57	65	61	57	56			56
8	76	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52			52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49			49
10	68	58	52	48	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	234082
5°	227734
10°	208101
15°	182294
20°	156370
25°	130556
30°	104472
35°	78354
40°	56878
45°	37182
50°	23266
55°	15713
60°	13902
65°	12816
70°	12053
75°	10929
80°	10355
85°	8806

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 37182 cd/sqm



TEST NUMBER: P1274282
 CATALOG NUMBER: P3AS17R159830DE010 E3DLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.5	10.3
10°-20°	223.7	24.1
20°-30°	246.5	26.6
30°-40°	184.6	19.9
40°-50°	95.7	10.3
50°-60°	39.6	4.3
60°-70°	24.6	2.6
70°-80°	13.8	1.5
80°-90°	4.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	565.7	61.0
0°-40°	750.3	80.9
0°-60°	885.6	95.4
0°-90°	928.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	928.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1068	
5°	1035	95
15°	803	224
25°	540	246
35°	293	185
45°	120	96
55°	41	40
65°	25	25
75°	13	14
85°	4	4
90°	0	



TEST NUMBER: P1274282
CATALOG NUMBER: P3AS17R159830DE010 E3DLD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1067.5
1°	1068.6
2°	1065.1
3°	1058.1
4°	1047.5
5°	1034.6
6°	1018.1
7°	1000.5
8°	979.3
9°	957.0
10°	934.6
12.5°	870.0
15°	803.0
17.5°	735.9
20°	670.1
22.5°	603.1
25°	539.6
27.5°	476.1
30°	412.6
32.5°	350.3
35°	292.7
37.5°	243.4
40°	198.7
42.5°	157.5
45°	119.9
47.5°	90.5
50°	68.2
52.5°	50.6
55°	41.1
57.5°	36.4
60°	31.7
62.5°	28.2
65°	24.7
67.5°	21.2
70°	18.8
72.5°	15.3
75°	12.9
77.5°	10.6
80°	8.2
82.5°	5.9
85°	3.5
87.5°	1.2
90°	0.0

(END OF REPORT)