

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273097

Luminaire Tested: P3AS02R509830DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273097
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R509830DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 98CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 99.0 lumens
Efficiency: N/A
Efficacy: 27.5 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273097

CATALOG NUMBER: P3AS02R509830DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1273097

CATALOG NUMBER: P3AS02R509830DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93
3	103	97	92	88	101	95	91	87	93	89	86		90	87	84		88
4	98	91	85	81	96	90	85	81	87	83	80		85	82	79		84
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79
6	89	80	75	71	88	80	74	70	78	73	70		77	73	69		75
7	85	76	70	66	84	75	70	66	74	69	66		73	69	65		72
8	81	72	66	62	80	71	66	62	70	65	62		69	65	62		68
9	78	68	63	59	76	68	62	59	67	62	59		66	62	58		65
10	74	65	59	56	73	65	59	56	64	59	55		63	58	55		62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	31511
5°	30883
10°	28924
15°	25903
20°	21795
25°	16622
30°	10812
35°	6398
40°	3693
45°	1861
50°	682
55°	535
60°	482
65°	467
70°	449
75°	424
80°	505
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1861 cd/sqm

TEST NUMBER: P1273097

CATALOG NUMBER: P3AS02R509830DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	13.1	13.2
10°-20°	31.5	31.9
20°-30°	30.9	31.3
30°-40°	15.6	15.7
40°-50°	4.9	5.0
50°-60°	1.3	1.3
60°-70°	0.9	0.9
70°-80°	0.5	0.5
80°-90°	0.2	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	75.5	76.3
0°-40°	91.1	92.1
0°-60°	97.3	98.3
0°-90°	99.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	99.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	144	
5°	140	13
15°	114	32
25°	69	31
35°	24	16
45°	6	5
55°	1	1
65°	1	1
75°	0	1
85°	0	0
90°	0	

TEST NUMBER: P1273097

CATALOG NUMBER: P3AS02R509830DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	143.7
2.5°	142.9
5°	140.3
7.5°	135.7
10°	129.9
12.5°	122.4
15°	114.1
17.5°	104.4
20°	93.4
22.5°	81.5
25°	68.7
27.5°	55.2
30°	42.7
32.5°	32.1
35°	23.9
37.5°	17.7
40°	12.9
42.5°	9.2
45°	6.0
47.5°	3.4
50°	2.0
52.5°	1.5
55°	1.4
57.5°	1.2
60°	1.1
62.5°	1.1
65°	0.9
67.5°	0.8
70°	0.7
72.5°	0.6
75°	0.5
77.5°	0.4
80°	0.4
82.5°	0.3
85°	0.2
87.5°	0.1
90°	0.0

(END OF REPORT)