

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273103

Luminaire Tested: P3AS02R509830DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273103
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R509830DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 98CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 77.0 lumens
Efficiency: N/A
Efficacy: 21.4 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273103

CATALOG NUMBER: P3AS02R509830DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1273103

CATALOG NUMBER: P3AS02R509830DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	101	99		99	97	96		95
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	92	86	81	97	90	85	81	88	83	79		85	81	78		83
4	93	85	78	73	91	83	77	73	81	76	72		79	75	71		77
5	88	78	72	67	86	77	71	66	75	70	66		74	69	65		72
6	83	73	66	61	81	72	65	61	70	65	60		69	64	60		67
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63
8	74	63	57	52	73	63	56	52	61	56	52		60	55	51		59
9	70	59	53	48	69	59	52	48	58	52	48		57	52	48		56
10	66	56	49	45	65	55	49	45	54	49	45		54	48	45		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	15657
5°	15408
10°	14740
15°	13644
20°	12274
25°	10791
30°	9166
35°	7442
40°	5582
45°	3597
50°	1706
55°	1338
60°	1272
65°	1193
70°	1090
75°	932
80°	884
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3597 cd/sqm

TEST NUMBER: P1273103

CATALOG NUMBER: P3AS02R509830DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	6.6	8.5
10°-20°	16.8	21.8
20°-30°	20.4	26.4
30°-40°	17.3	22.4
40°-50°	9.0	11.6
50°-60°	3.2	4.2
60°-70°	2.2	2.9
70°-80°	1.2	1.6
80°-90°	0.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	43.7	56.7
0°-40°	61.0	79.2
0°-60°	73.2	95.0
0°-90°	77.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	77.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	71	
5°	70	7
15°	60	17
25°	45	20
35°	28	17
45°	12	9
55°	4	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1273103

CATALOG NUMBER: P3AS02R509830DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	71.4
2.5°	71.1
5°	70.0
7.5°	68.5
10°	66.2
12.5°	63.3
15°	60.1
17.5°	56.5
20°	52.6
22.5°	48.5
25°	44.6
27.5°	40.4
30°	36.2
32.5°	32.0
35°	27.8
37.5°	23.6
40°	19.5
42.5°	15.6
45°	11.6
47.5°	7.7
50°	5.0
52.5°	3.9
55°	3.5
57.5°	3.2
60°	2.9
62.5°	2.5
65°	2.3
67.5°	1.9
70°	1.7
72.5°	1.4
75°	1.1
77.5°	0.9
80°	0.7
82.5°	0.5
85°	0.4
87.5°	0.2
90°	0.0

(END OF REPORT)