

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273195

Luminaire Tested: P3AS02R659830DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273195
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R659830DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 98CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 141.0 lumens
Efficiency: N/A
Efficacy: 39.2 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273195

CATALOG NUMBER: P3AS02R659830DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1273195

CATALOG NUMBER: P3AS02R659830DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	25086
5°	24763
10°	23914
15°	22565
20°	20815
25°	18896
30°	16737
35°	14241
40°	11336
45°	8001
50°	4640
55°	2523
60°	2368
65°	2127
70°	1923
75°	1779
80°	1642
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 8001 cd/sqm

TEST NUMBER: P1273195

CATALOG NUMBER: P3AS02R659830DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	10.6	7.5
10°-20°	27.8	19.7
20°-30°	35.7	25.3
30°-40°	33.1	23.4
40°-50°	20.0	14.2
50°-60°	6.8	4.8
60°-70°	4.1	2.9
70°-80°	2.3	1.6
80°-90°	0.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	74.1	52.6
0°-40°	107.2	76.0
0°-60°	134.0	95.0
0°-90°	141.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	141.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	114	
5°	112	11
15°	99	28
25°	78	36
35°	53	33
45°	26	20
55°	7	7
65°	4	4
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1273195

CATALOG NUMBER: P3AS02R659830DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	114.4
2.5°	113.9
5°	112.5
7.5°	110.3
10°	107.4
12.5°	103.9
15°	99.4
17.5°	94.5
20°	89.2
22.5°	83.6
25°	78.1
27.5°	72.2
30°	66.1
32.5°	60.0
35°	53.2
37.5°	46.6
40°	39.6
42.5°	32.6
45°	25.8
47.5°	19.5
50°	13.6
52.5°	8.6
55°	6.6
57.5°	5.9
60°	5.4
62.5°	4.7
65°	4.1
67.5°	3.6
70°	3.0
72.5°	2.7
75°	2.1
77.5°	1.8
80°	1.3
82.5°	0.9
85°	0.5
87.5°	0.4
90°	0.0

(END OF REPORT)