

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273250

Luminaire Tested: P3AS05R159830DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273250
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R159830DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 98CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 112.0 lumens
Efficiency: N/A
Efficacy: 15.6 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273250

CATALOG NUMBER: P3AS05R159830DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1273250

CATALOG NUMBER: P3AS05R159830DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	106	111	108	106	104	104	102	101		100	99	98		97
2	108	103	98	95	105	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	93	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	87	79	73	69	77	72	69		76	71	68		74
7	84	75	69	65	83	74	69	65	73	68	64		72	67	64		71
8	80	71	65	61	79	71	65	61	69	64	61		68	64	61		67
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64
10	74	64	59	55	73	64	59	55	63	58	55		62	58	55		62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	48308
5°	44640
10°	35648
15°	26924
20°	20488
25°	15630
30°	11192
35°	7308
40°	4466
45°	2698
50°	1808
55°	1376
60°	1184
65°	1038
70°	962
75°	932
80°	631
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2698 cd/sqm

TEST NUMBER: P1273250

CATALOG NUMBER: P3AS05R159830DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	18.0	16.0
10°-20°	33.1	29.6
20°-30°	29.5	26.3
30°-40°	17.5	15.6
40°-50°	7.1	6.4
50°-60°	3.4	3.0
60°-70°	2.1	1.8
70°-80°	1.1	1.0
80°-90°	0.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	80.6	72.0
0°-40°	98.1	87.6
0°-60°	108.6	96.9
0°-90°	112.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	112.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	220	
5°	203	18
15°	119	33
25°	65	30
35°	27	17
45°	9	7
55°	4	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1273250

CATALOG NUMBER: P3AS05R159830DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	220.3
1°	219.7
2°	218.1
3°	214.8
4°	209.3
5°	202.8
6°	195.7
7°	187.3
8°	178.6
9°	169.7
10°	160.1
12.5°	138.0
15°	118.6
17.5°	101.9
20°	87.8
22.5°	75.5
25°	64.6
27.5°	54.0
30°	44.2
32.5°	35.3
35°	27.3
37.5°	20.9
40°	15.6
42.5°	11.6
45°	8.7
47.5°	6.7
50°	5.3
52.5°	4.4
55°	3.6
57.5°	3.1
60°	2.7
62.5°	2.4
65°	2.0
67.5°	1.8
70°	1.5
72.5°	1.3
75°	1.1
77.5°	0.7
80°	0.5
82.5°	0.4
85°	0.2
87.5°	0.2
90°	0.0

(END OF REPORT)