

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274361

Luminaire Tested: P3AS17R309830DE010 E3D1WH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274361
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R309830DE010 E3D1WH
Description: 3in Adjustable LED luminaire with, R30 optic, 3000K CCT AND, 98CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1484.0 lumens
Efficiency: N/A
Efficacy: 72.7 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274361

CATALOG NUMBER: P3AS17R309830DE010 E3D1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1274361

CATALOG NUMBER: P3AS17R309830DE010 E3D1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	96	95
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	94	93	92
3	108	103	100	97	106	102	99	96	99	97	95	97	95	93	95	93	92	90	89	88
4	105	99	95	92	103	98	95	92	96	93	91	94	92	90	93	91	89	88	87	86
5	101	96	92	89	100	95	91	88	93	90	87	92	89	87	90	88	86	85	84	83
6	99	92	88	85	97	92	88	85	90	87	84	89	86	84	88	85	83	82	81	80
7	96	89	85	82	95	89	85	82	88	84	82	87	84	81	86	83	81	80	79	78
8	93	87	83	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78	77	76
9	91	84	80	77	90	84	80	77	83	79	77	82	79	77	82	79	77	76	75	74
10	88	82	78	75	88	81	78	75	81	77	75	80	77	75	80	77	75	74	73	72

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1180717
5°	1165328
10°	1017438
15°	646678
20°	256222
25°	85578
30°	39829
35°	18042
40°	6927
45°	3380
50°	989
55°	459
60°	263
65°	311
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3380 cd/sqm

TEST NUMBER: P1274361

CATALOG NUMBER: P3AS17R309830DE010 E3D1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	484.0	32.6
10°-20°	750.6	50.6
20°-30°	193.5	13.0
30°-40°	45.5	3.1
40°-50°	8.9	0.6
50°-60°	1.0	0.1
60°-70°	0.5	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1428.1	96.2
0°-40°	1473.6	99.3
0°-60°	1483.5	100.0
0°-90°	1484.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1484.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5384	
5°	5294	484
15°	2849	751
25°	354	194
35°	67	45
45°	11	9
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1274361

CATALOG NUMBER: P3AS17R309830DE010 E3D1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	5384.5
1°	5380.5
2°	5367.8
3°	5353.4
4°	5332.1
5°	5294.1
6°	5232.4
7°	5129.9
8°	4989.9
9°	4807.3
10°	4569.4
11°	4286.5
12°	3977.7
13°	3622.3
14°	3250.2
15°	2848.6
16°	2455.2
17°	2076.1
18°	1712.6
19°	1379.1
20°	1098.0
21°	864.1
22°	679.8
23°	538.0
24°	430.9
25°	353.7
26°	294.9
27°	250.6
28°	216.6
29°	185.5
30°	157.3
32.5°	99.1
35°	67.4
37.5°	42.1
40°	24.2
42.5°	16.1
45°	10.9
47.5°	6.3
50°	2.9
52.5°	1.2
55°	1.2
57.5°	0.6
60°	0.6
62.5°	0.6
65°	0.6



TEST NUMBER: P1274361

CATALOG NUMBER: P3AS17R309830DE010 E3D1WH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.6
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)