

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274388

Luminaire Tested: P3AS17R359830DE010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274388
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R359830DE010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R35 optic, 3000K CCT AND, 98CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1491.9 lumens
Efficiency: N/A
Efficacy: 73.1 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274388

CATALOG NUMBER: P3AS17R359830DE010 E3CD1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1274388

CATALOG NUMBER: P3AS17R359830DE010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96		
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	93		
3	107	102	98	95	105	101	97	95	98	96	93	96	94	92	94	92	90	89		
4	104	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	86		
5	100	94	90	87	99	93	89	86	92	88	86	90	87	85	89	86	84	83		
6	97	91	86	83	96	90	86	83	89	85	82	87	84	82	86	83	81	80		
7	94	87	83	80	93	87	83	80	86	82	79	85	81	79	84	81	79	78		
8	91	84	80	77	90	84	80	77	83	79	77	82	79	76	81	78	76	75		
9	89	82	77	74	88	81	77	74	80	77	74	80	76	74	79	76	74	73		
10	86	79	75	72	85	79	75	72	78	74	72	77	74	72	77	74	71	70		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	972883
5°	953068
10°	886646
15°	650038
20°	332856
25°	119959
30°	46716
35°	16356
40°	6727
45°	1830
50°	1603
55°	1797
60°	1535
65°	1193
70°	1475
75°	1949
80°	1515
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 82.5°

Luminance: 2016 cd/sqm

TEST NUMBER: P1274388

CATALOG NUMBER: P3AS17R359830DE010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	403.6	27.1
10°-20°	757.3	50.8
20°-30°	268.1	18.0
30°-40°	47.0	3.1
40°-50°	6.9	0.5
50°-60°	3.8	0.3
60°-70°	2.7	0.2
70°-80°	2.0	0.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1429.1	95.8
0°-40°	1476.1	98.9
0°-60°	1486.7	99.7
0°-90°	1491.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1491.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4437	
5°	4330	404
15°	2863	757
25°	496	268
35°	61	47
45°	6	7
55°	5	4
65°	2	3
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1274388

CATALOG NUMBER: P3AS17R359830DE010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	4436.7
1°	4435.5
2°	4421.4
3°	4394.4
4°	4369.7
5°	4329.8
6°	4288.7
7°	4242.8
8°	4186.4
9°	4098.3
10°	3982.0
11°	3821.0
12°	3627.1
13°	3396.8
14°	3143.1
15°	2863.4
17.5°	2132.6
20°	1426.4
22.5°	860.1
25°	495.8
27.5°	296.1
30°	184.5
32.5°	106.9
35°	61.1
37.5°	38.8
40°	23.5
42.5°	11.7
45°	5.9
47.5°	4.7
50°	4.7
52.5°	4.7
55°	4.7
57.5°	3.5
60°	3.5
62.5°	3.5
65°	2.3
67.5°	2.3
70°	2.3
72.5°	2.3
75°	2.3
77.5°	1.2
80°	1.2
82.5°	1.2
85°	0.0
87.5°	0.0



TEST NUMBER: P1274388

CATALOG NUMBER: P3AS17R359830DE010 E3CD1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)