

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274392

Luminaire Tested: P3AS17R359830DE010 E3DL1H

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1274392  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R359830DE010 E3DL1H  
Description: 3in Adjustable LED luminaire with, R35 optic, 3000K CCT AND, 98CRI , E3DL1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1234.9 lumens  
Efficiency: N/A  
Efficacy: 60.5 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 20.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1274392  
CATALOG NUMBER: P3AS17R359830DE010 E3DL1H

### Luminous Intensity Polar Plot





TEST NUMBER: P1274392  
 CATALOG NUMBER: P3AS17R359830DE010 E3DL1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	90	90	90	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85	85	85	85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80	80	80	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76	76	76	76
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73	73	73	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	70	70	70	70
8	85	77	72	69	84	77	72	69	76	71	68	75	71	68	74	70	68	67	67	67	67
9	82	74	69	66	81	74	69	65	73	68	65	72	68	65	71	68	65	64	64	64	64
10	79	71	66	63	78	71	66	63	70	66	63	69	65	62	69	65	62	61	61	61	61

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	622889
5°	598634
10°	521589
15°	399503
20°	267283
25°	161719
30°	92799
35°	51879
40°	27566
45°	14203
50°	6823
55°	5390
60°	5131
65°	4255
70°	4488
75°	3982
80°	4420
85°	3019

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 14203 cd/sqm



TEST NUMBER: P1274392  
 CATALOG NUMBER: P3AS17R359830DE010 E3DL1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	247.4	20.0
10°-20°	479.5	38.8
20°-30°	313.9	25.4
30°-40°	127.3	10.3
40°-50°	38.2	3.1
50°-60°	13.0	1.1
60°-70°	8.7	0.7
70°-80°	5.1	0.4
80°-90°	1.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1040.9	84.3
0°-40°	1168.2	94.6
0°-60°	1219.4	98.7
0°-90°	1234.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1234.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2841	
5°	2720	247
15°	1760	480
25°	668	314
35°	194	127
45°	46	38
55°	14	13
65°	8	9
75°	5	5
85°	1	2
90°	0	



TEST NUMBER: P1274392  
CATALOG NUMBER: P3AS17R359830DE010 E3DL1H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2840.6
1°	2835.9
2°	2822.9
3°	2797.1
4°	2766.6
5°	2719.6
6°	2660.8
7°	2595.0
8°	2521.0
9°	2436.4
10°	2342.5
11°	2237.9
12°	2128.7
13°	2006.5
14°	1890.2
15°	1759.8
17.5°	1443.8
20°	1145.4
22.5°	881.1
25°	668.4
27.5°	498.1
30°	366.5
32.5°	269.0
35°	193.8
37.5°	137.4
40°	96.3
42.5°	67.0
45°	45.8
47.5°	30.5
50°	20.0
52.5°	15.3
55°	14.1
57.5°	12.9
60°	11.7
62.5°	10.6
65°	8.2
67.5°	7.0
70°	7.0
72.5°	5.9
75°	4.7
77.5°	3.5
80°	3.5
82.5°	2.3
85°	1.2
87.5°	1.2



TEST NUMBER: P1274392  
CATALOG NUMBER: P3AS17R359830DE010 E3DL1H

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)