

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274423

Luminaire Tested: P3AS17R409830DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274423
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R409830DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R40 optic, 3000K CCT AND, 98CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 671.1 lumens
Efficiency: N/A
Efficacy: 32.9 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274423
CATALOG NUMBER: P3AS17R409830DE010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1274423

CATALOG NUMBER: P3AS17R409830DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	96	96	96	94
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	91	91	91	89
3	104	99	94	91	102	97	93	90	95	91	88	92	89	87	90	88	86	86	86	86	84
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	81	81	81	80
5	96	88	83	79	94	88	83	79	86	82	78	84	81	78	83	80	77	77	77	77	76
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	73	73	73	72
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	70	70	70	69
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	67	67	67	65
9	82	73	68	64	81	73	68	64	72	67	64	71	67	64	70	66	64	64	64	64	63
10	78	70	65	62	78	70	65	61	69	64	61	68	64	61	67	64	61	61	61	61	60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	296906
5°	288289
10°	261607
15°	216119
20°	155904
25°	96417
30°	52211
35°	26983
40°	14685
45°	8218
50°	4128
55°	3097
60°	2763
65°	2698
70°	2565
75°	2457
80°	2147
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8218 cd/sqm



TEST NUMBER: P1274423
 CATALOG NUMBER: P3AS17R409830DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.7	18.0
10°-20°	259.2	38.6
20°-30°	185.0	27.6
30°-40°	68.1	10.2
40°-50°	21.5	3.2
50°-60°	7.5	1.1
60°-70°	5.1	0.8
70°-80°	3.0	0.5
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	565.0	84.2
0°-40°	633.1	94.3
0°-60°	662.0	98.6
0°-90°	671.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	671.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1354	
5°	1310	121
15°	952	259
25°	398	185
35°	101	68
45°	26	21
55°	8	7
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1274423
CATALOG NUMBER: P3AS17R409830DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1354.0
2.5°	1343.7
5°	1309.7
7.5°	1253.2
10°	1174.9
12.5°	1075.3
15°	952.0
17.5°	813.8
20°	668.1
22.5°	524.7
25°	398.5
27.5°	292.6
30°	206.2
32.5°	144.6
35°	100.8
37.5°	71.4
40°	51.3
42.5°	36.9
45°	26.5
47.5°	17.9
50°	12.1
52.5°	8.6
55°	8.1
57.5°	7.5
60°	6.3
62.5°	5.8
65°	5.2
67.5°	4.6
70°	4.0
72.5°	3.5
75°	2.9
77.5°	2.3
80°	1.7
82.5°	1.2
85°	0.6
87.5°	0.6
90°	0.0

(END OF REPORT)