

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274424

Luminaire Tested: P3AS17R409830DE010 E3DL1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274424
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R409830DE010 E3DL1H
Description: 3in Adjustable LED luminaire with, R40 optic, 3000K CCT AND, 98CRI , E3DL1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1369.1 lumens
Efficiency: N/A
Efficacy: 67.1 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274424

CATALOG NUMBER: P3AS17R409830DE010 E3DL1H

Luminous Intensity Polar Plot



TEST NUMBER: P1274424

CATALOG NUMBER: P3AS17R409830DE010 E3DL1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	112	109	107	105	105	104	102		102	100	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	104	99	94	91	102	97	93	90	95	91	88		92	89	87		90
4	100	93	88	85	98	92	88	84	90	86	83		88	85	82		86
5	96	88	83	79	94	88	83	79	86	82	78		84	81	78		83
6	92	84	79	75	91	83	78	75	82	78	74		81	77	74		79
7	88	80	75	71	87	79	74	71	78	74	71		77	73	70		76
8	85	76	71	68	84	76	71	67	75	70	67		74	70	67		73
9	82	73	68	64	81	73	68	64	72	67	64		71	67	64		70
10	78	70	65	62	78	70	65	61	69	64	61		68	64	61		67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	605763
5°	588178
10°	533747
15°	440956
20°	318084
25°	196729
30°	106523
35°	55038
40°	29942
45°	16777
50°	8426
55°	6308
60°	5657
65°	5500
70°	5257
75°	4999
80°	4420
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16777 cd/sqm

TEST NUMBER: P1274424

CATALOG NUMBER: P3AS17R409830DE010 E3DL1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	246.3	18.0
10°-20°	528.9	38.6
20°-30°	377.4	27.6
30°-40°	138.9	10.1
40°-50°	43.8	3.2
50°-60°	15.2	1.1
60°-70°	10.5	0.8
70°-80°	6.2	0.5
80°-90°	1.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1152.7	84.2
0°-40°	1291.6	94.3
0°-60°	1350.6	98.7
0°-90°	1369.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1369.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2762	
5°	2672	246
15°	1942	529
25°	813	377
35°	206	139
45°	54	44
55°	16	15
65°	11	10
75°	6	6
85°	1	2
90°	0	

TEST NUMBER: P1274424

CATALOG NUMBER: P3AS17R409830DE010 E3DL1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	2762.5
2.5°	2741.4
5°	2672.1
7.5°	2556.9
10°	2397.1
12.5°	2193.8
15°	1942.4
17.5°	1660.3
20°	1363.1
22.5°	1070.5
25°	813.1
27.5°	596.9
30°	420.7
32.5°	294.9
35°	205.6
37.5°	145.7
40°	104.6
42.5°	75.2
45°	54.1
47.5°	36.4
50°	24.7
52.5°	17.6
55°	16.5
57.5°	15.3
60°	12.9
62.5°	11.8
65°	10.6
67.5°	9.4
70°	8.2
72.5°	7.1
75°	5.9
77.5°	4.7
80°	3.5
82.5°	2.4
85°	1.2
87.5°	1.2
90°	0.0

(END OF REPORT)