

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273516

Luminaire Tested: P3AS05R609830DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273516
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R609830DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 98CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 389.0 lumens
Efficiency: N/A
Efficacy: 54.0 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273516

CATALOG NUMBER: P3AS05R609830DE010 E3DLP1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1273516

CATALOG NUMBER: P3AS05R609830DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	91	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		78	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		68
8	77	68	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	60	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	91857
5°	90975
10°	88331
15°	82747
20°	73250
25°	61286
30°	48033
35°	34827
40°	23186
45°	14451
50°	7812
55°	2256
60°	2105
65°	1920
70°	1923
75°	1864
80°	1894
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14451 cd/sqm

TEST NUMBER: P1273516

CATALOG NUMBER: P3AS05R609830DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.9	10.0
10°-20°	101.1	26.0
20°-30°	115.3	29.6
30°-40°	81.8	21.0
40°-50°	37.1	9.5
50°-60°	7.9	2.0
60°-70°	3.8	1.0
70°-80°	2.3	0.6
80°-90°	0.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	255.3	65.6
0°-40°	337.1	86.7
0°-60°	382.1	98.2
0°-90°	389.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	389.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	419	
5°	413	39
15°	364	101
25°	253	115
35°	130	82
45°	47	37
55°	6	8
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1273516

CATALOG NUMBER: P3AS05R609830DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	418.9
2.5°	417.4
5°	413.3
7.5°	406.3
10°	396.7
12.5°	383.0
15°	364.5
17.5°	341.3
20°	313.9
22.5°	284.3
25°	253.3
27.5°	221.5
30°	189.7
32.5°	159.4
35°	130.1
37.5°	104.3
40°	81.0
42.5°	61.4
45°	46.6
47.5°	34.8
50°	22.9
52.5°	10.7
55°	5.9
57.5°	5.2
60°	4.8
62.5°	4.4
65°	3.7
67.5°	3.3
70°	3.0
72.5°	2.6
75°	2.2
77.5°	1.8
80°	1.5
82.5°	1.1
85°	0.7
87.5°	0.4
90°	0.0

(END OF REPORT)