

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273541

Luminaire Tested: P3AS05R659830DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273541
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R659830DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 98CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 126.0 lumens
Efficiency: N/A
Efficacy: 17.5 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273541

CATALOG NUMBER: P3AS05R659830DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1273541

CATALOG NUMBER: P3AS05R659830DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		90
3	101	94	88	84	99	92	87	83	90	85	82		87	84	81		85
4	95	87	81	76	93	86	80	76	84	79	75		82	78	74		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		71
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		59
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	32037
5°	31235
10°	29080
15°	26061
20°	22519
25°	18727
30°	14762
35°	10949
40°	7528
45°	4683
50°	2524
55°	1606
60°	1360
65°	1245
70°	1026
75°	932
80°	884
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4683 cd/sqm

TEST NUMBER: P1273541

CATALOG NUMBER: P3AS05R659830DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	13.2	10.5
10°-20°	31.9	25.3
20°-30°	35.3	28.0
30°-40°	25.6	20.3
40°-50°	12.0	9.5
50°-60°	4.0	3.2
60°-70°	2.3	1.9
70°-80°	1.2	1.0
80°-90°	0.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	80.4	63.8
0°-40°	106.0	84.1
0°-60°	122.0	96.9
0°-90°	126.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	126.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	146	
5°	142	13
15°	115	32
25°	77	35
35°	41	26
45°	15	12
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1273541

CATALOG NUMBER: P3AS05R659830DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	146.1
2.5°	145.1
5°	141.9
7.5°	137.0
10°	130.6
12.5°	123.2
15°	114.8
17.5°	105.7
20°	96.5
22.5°	86.8
25°	77.4
27.5°	67.8
30°	58.3
32.5°	49.2
35°	40.9
37.5°	33.2
40°	26.3
42.5°	20.2
45°	15.1
47.5°	10.9
50°	7.4
52.5°	5.1
55°	4.2
57.5°	3.6
60°	3.1
62.5°	2.7
65°	2.4
67.5°	2.0
70°	1.6
72.5°	1.5
75°	1.1
77.5°	0.9
80°	0.7
82.5°	0.5
85°	0.4
87.5°	0.2
90°	0.0

(END OF REPORT)