

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273543

Luminaire Tested: P3AS05R659830DE010 E3DLP1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273543
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R659830DE010 E3DLP1LI
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 98CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 257.0 lumens
Efficiency: N/A
Efficacy: 35.7 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273543
CATALOG NUMBER: P3AS05R659830DE010 E3DLP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1273543
 CATALOG NUMBER: P3AS05R659830DE010 E3DLP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92				92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	90	88	86	85				85
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78				78
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72				72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66				66
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62				62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57				57
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54				54
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50				50
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47				47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	65324
5°	63702
10°	59318
15°	53167
20°	45924
25°	38180
30°	30106
35°	22326
40°	15372
45°	9551
50°	5185
55°	3250
60°	2763
65°	2491
70°	2116
75°	1864
80°	1894
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9551 cd/sqm



TEST NUMBER: P1273543
 CATALOG NUMBER: P3AS05R659830DE010 E3DLP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	26.9	10.5
10°-20°	65.1	25.3
20°-30°	72.0	28.0
30°-40°	52.3	20.3
40°-50°	24.5	9.5
50°-60°	8.2	3.2
60°-70°	4.8	1.9
70°-80°	2.5	1.0
80°-90°	0.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	163.9	63.8
0°-40°	216.2	84.1
0°-60°	248.9	96.9
0°-90°	257.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	257.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	298	
5°	289	27
15°	234	65
25°	158	72
35°	83	52
45°	31	24
55°	8	8
65°	5	5
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P1273543
CATALOG NUMBER: P3AS05R659830DE010 E3DLP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	297.9
2.5°	296.1
5°	289.4
7.5°	279.4
10°	266.4
12.5°	251.2
15°	234.2
17.5°	215.6
20°	196.8
22.5°	177.1
25°	157.8
27.5°	138.2
30°	118.9
32.5°	100.4
35°	83.4
37.5°	67.8
40°	53.7
42.5°	41.1
45°	30.8
47.5°	22.2
50°	15.2
52.5°	10.4
55°	8.5
57.5°	7.4
60°	6.3
62.5°	5.6
65°	4.8
67.5°	4.1
70°	3.3
72.5°	3.0
75°	2.2
77.5°	1.9
80°	1.5
82.5°	1.1
85°	0.7
87.5°	0.4
90°	0.0

(END OF REPORT)