

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274594

Luminaire Tested: P3AS17R709830DE010 E3DL1H

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1274594  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R709830DE010 E3DL1H  
Description: 3in Adjustable LED luminaire with, R70 optic, 3000K CCT AND, 98CRI , E3DL1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1182.9 lumens  
Efficiency: N/A  
Efficacy: 58.0 lumens/watt  
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 20.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1274594  
CATALOG NUMBER: P3AS17R709830DE010 E3DL1H

### Luminous Intensity Polar Plot





TEST NUMBER: P1274594  
 CATALOG NUMBER: P3AS17R709830DE010 E3DL1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84	84	84	84
3	100	93	88	83	98	92	87	82	89	85	81	86	83	80	84	81	79	77	77	77	77
4	94	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	70	70	70	70
5	89	80	73	69	87	79	73	68	77	72	68	75	71	67	74	70	66	65	65	65	65
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60	60	60	60
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55	55	55	55
8	75	65	58	53	74	64	58	53	63	57	53	62	57	53	61	56	53	51	51	51	51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48	48	48	48
10	67	57	50	46	66	56	50	46	55	50	46	55	49	46	54	49	46	44	44	44	44

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	229017
5°	226282
10°	219724
15°	210421
20°	197114
25°	179067
30°	154682
35°	123272
40°	89797
45°	59014
50°	27666
55°	8525
60°	8245
65°	7939
70°	7501
75°	7964
80°	7450
85°	5787

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 59014 cd/sqm



TEST NUMBER: P1274594  
 CATALOG NUMBER: P3AS17R709830DE010 E3DL1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	96.8	8.2
10°-20°	259.4	21.9
20°-30°	337.2	28.5
30°-40°	286.1	24.2
40°-50°	147.5	12.5
50°-60°	28.4	2.4
60°-70°	15.4	1.3
70°-80°	9.4	0.8
80°-90°	2.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	693.4	58.6
0°-40°	979.5	82.8
0°-60°	1155.4	97.7
0°-90°	1182.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1182.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1044	
5°	1028	97
15°	927	259
25°	740	337
35°	460	286
45°	190	148
55°	22	28
65°	15	15
75°	9	9
85°	2	3
90°	0	



TEST NUMBER: P1274594  
CATALOG NUMBER: P3AS17R709830DE010 E3DL1H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1044.4
2.5°	1040.9
5°	1028.0
7.5°	1009.2
10°	986.8
12.5°	958.6
15°	926.9
17.5°	888.2
20°	844.7
22.5°	795.3
25°	740.1
27.5°	677.9
30°	610.9
32.5°	536.9
35°	460.5
37.5°	385.3
40°	313.7
42.5°	246.7
45°	190.3
47.5°	139.8
50°	81.1
52.5°	35.2
55°	22.3
57.5°	21.1
60°	18.8
62.5°	17.6
65°	15.3
67.5°	14.1
70°	11.7
72.5°	10.6
75°	9.4
77.5°	7.0
80°	5.9
82.5°	3.5
85°	2.3
87.5°	1.2
90°	0.0

(END OF REPORT)