

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273545

Luminaire Tested: P3AS05R659830DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273545
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R659830DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 98CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 371.0 lumens
Efficiency: N/A
Efficacy: 51.5 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273545
CATALOG NUMBER: P3AS05R659830DE010 E3DLP1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1273545
 CATALOG NUMBER: P3AS05R659830DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93				93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85				85
3	101	95	89	85	99	93	88	84	90	86	83	88	85	82	86	83	80	79				79
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	74	73				73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	68				68
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	67	64	63				63
7	82	72	66	61	80	71	65	61	70	64	61	69	64	60	67	63	60	58				58
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55				55
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51				51
10	70	60	54	50	69	59	54	50	59	53	50	58	53	50	57	53	49	48				48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	87493
5°	86440
10°	83165
15°	77912
20°	70076
25°	59495
30°	46539
35°	33167
40°	21698
45°	13428
50°	6823
55°	2409
60°	2105
65°	2127
70°	1923
75°	1864
80°	1894
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 13428 cd/sqm



TEST NUMBER: P1273545
 CATALOG NUMBER: P3AS05R659830DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.9	9.9
10°-20°	95.5	25.7
20°-30°	111.6	30.1
30°-40°	78.0	21.0
40°-50°	34.3	9.3
50°-60°	7.6	2.1
60°-70°	3.9	1.0
70°-80°	2.3	0.6
80°-90°	0.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	244.0	65.8
0°-40°	322.0	86.8
0°-60°	364.0	98.1
0°-90°	371.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	371.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	399	
5°	393	37
15°	343	96
25°	246	112
35°	124	78
45°	43	34
55°	6	8
65°	4	4
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1273545
CATALOG NUMBER: P3AS05R659830DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	399.0
2.5°	397.5
5°	392.7
7.5°	384.6
10°	373.5
12.5°	359.8
15°	343.2
17.5°	322.8
20°	300.3
22.5°	274.8
25°	245.9
27.5°	215.6
30°	183.8
32.5°	153.1
35°	123.9
37.5°	98.4
40°	75.8
42.5°	57.3
45°	43.3
47.5°	31.8
50°	20.0
52.5°	10.4
55°	6.3
57.5°	5.5
60°	4.8
62.5°	4.4
65°	4.1
67.5°	3.3
70°	3.0
72.5°	2.6
75°	2.2
77.5°	1.8
80°	1.5
82.5°	1.1
85°	0.7
87.5°	0.4
90°	0.0

(END OF REPORT)