

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273616

Luminaire Tested: P3AS09R209830DE010 E3DL1H

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1273616  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R209830DE010 E3DL1H  
Description: 3in Adjustable LED luminaire with, R20 optic, 3000K CCT AND, 98CRI , E3DL1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 566.0 lumens  
Efficiency: N/A  
Efficacy: 51.5 lumens/watt  
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 11  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1273616

CATALOG NUMBER: P3AS09R209830DE010 E3DL1H

### Luminous Intensity Polar Plot



TEST NUMBER: P1273616

CATALOG NUMBER: P3AS09R209830DE010 E3DL1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 114 | 112 | 110 | 108 | 112 | 110 | 108 | 106 | 106 | 104 | 103 |  | 102 | 101 | 100 |  | 99  |
| 2   | 110 | 106 | 102 | 100 | 108 | 104 | 101 | 98  | 101 | 98  | 96  |  | 98  | 96  | 94  |  | 95  |
| 3   | 106 | 100 | 96  | 93  | 104 | 99  | 95  | 92  | 97  | 93  | 91  |  | 94  | 92  | 89  |  | 92  |
| 4   | 102 | 96  | 91  | 88  | 100 | 95  | 90  | 87  | 92  | 89  | 86  |  | 91  | 88  | 85  |  | 89  |
| 5   | 98  | 91  | 87  | 83  | 97  | 90  | 86  | 83  | 89  | 85  | 82  |  | 87  | 84  | 81  |  | 86  |
| 6   | 95  | 87  | 83  | 79  | 93  | 87  | 82  | 79  | 85  | 81  | 78  |  | 84  | 81  | 78  |  | 83  |
| 7   | 91  | 84  | 79  | 76  | 90  | 83  | 79  | 76  | 82  | 78  | 75  |  | 81  | 78  | 75  |  | 80  |
| 8   | 88  | 81  | 76  | 73  | 87  | 80  | 76  | 73  | 79  | 75  | 72  |  | 78  | 75  | 72  |  | 78  |
| 9   | 85  | 78  | 73  | 70  | 85  | 77  | 73  | 70  | 77  | 73  | 70  |  | 76  | 72  | 69  |  | 75  |
| 10  | 83  | 75  | 71  | 68  | 82  | 75  | 70  | 67  | 74  | 70  | 67  |  | 73  | 70  | 67  |  | 73  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 435469 |
| 5°  | 395861 |
| 10° | 292557 |
| 15° | 180977 |
| 20° | 103352 |
| 25° | 59011  |
| 30° | 33094  |
| 35° | 18016  |
| 40° | 9847   |
| 45° | 5427   |
| 50° | 3173   |
| 55° | 2294   |
| 60° | 2149   |
| 65° | 1972   |
| 70° | 1731   |
| 75° | 1864   |
| 80° | 1389   |
| 85° | 1258   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 45°  
Luminance: 5427 cd/sqm

TEST NUMBER: P1273616

CATALOG NUMBER: P3AS09R209830DE010 E3DL1H

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 155.7  | 27.5      |
| 10°-20°   | 222.3  | 39.3      |
| 20°-30°   | 116.0  | 20.5      |
| 30°-40°   | 44.9   | 7.9       |
| 40°-50°   | 14.6   | 2.6       |
| 50°-60°   | 5.7    | 1.0       |
| 60°-70°   | 3.8    | 0.7       |
| 70°-80°   | 2.2    | 0.4       |
| 80°-90°   | 0.7    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 494.1  | 87.3      |
| 0°-40°    | 539.0  | 95.2      |
| 0°-60°    | 559.3  | 98.8      |
| 0°-90°    | 566.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 566.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1986 |      |
| 5°  | 1798 | 156  |
| 15° | 797  | 222  |
| 25° | 244  | 116  |
| 35° | 67   | 45   |
| 45° | 18   | 15   |
| 55° | 6    | 6    |
| 65° | 4    | 4    |
| 75° | 2    | 2    |
| 85° | 0    | 1    |
| 90° | 0    |      |

TEST NUMBER: P1273616

CATALOG NUMBER: P3AS09R209830DE010 E3DL1H

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1985.9 |
| 1°    | 1982.1 |
| 2°    | 1958.6 |
| 3°    | 1922.5 |
| 4°    | 1866.7 |
| 5°    | 1798.4 |
| 6°    | 1717.4 |
| 7°    | 1627.8 |
| 8°    | 1523.9 |
| 9°    | 1422.7 |
| 10°   | 1313.9 |
| 12.5° | 1044.4 |
| 15°   | 797.2  |
| 17.5° | 596.5  |
| 20°   | 442.9  |
| 22.5° | 328.1  |
| 25°   | 243.9  |
| 27.5° | 179.9  |
| 30°   | 130.7  |
| 32.5° | 94.6   |
| 35°   | 67.3   |
| 37.5° | 48.7   |
| 40°   | 34.4   |
| 42.5° | 24.6   |
| 45°   | 17.5   |
| 47.5° | 12.6   |
| 50°   | 9.3    |
| 52.5° | 7.1    |
| 55°   | 6.0    |
| 57.5° | 5.5    |
| 60°   | 4.9    |
| 62.5° | 4.4    |
| 65°   | 3.8    |
| 67.5° | 3.3    |
| 70°   | 2.7    |
| 72.5° | 2.7    |
| 75°   | 2.2    |
| 77.5° | 1.6    |
| 80°   | 1.1    |
| 82.5° | 1.1    |
| 85°   | 0.5    |
| 87.5° | 0.5    |
| 90°   | 0.0    |

(END OF REPORT)