

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274602

Luminaire Tested: P3AS17R709830DE010 E3DLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274602
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R709830DE010 E3DLP1MW
Description: 3in Adjustable LED luminaire with, R70 optic, 3000K CCT AND, 98CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 845.0 lumens
Efficiency: N/A
Efficacy: 41.4 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274602

CATALOG NUMBER: P3AS17R709830DE010 E3DLP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1274602

CATALOG NUMBER: P3AS17R709830DE010 E3DLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	88	83	98	92	87	83	89	85	81		87	83	80		84
4	95	86	80	76	93	85	80	75	83	78	74		81	77	73		79
5	89	80	74	69	88	79	73	69	78	72	68		76	71	68		74
6	85	75	68	64	83	74	68	64	73	67	63		71	66	63		70
7	80	70	64	59	79	69	63	59	68	62	58		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	51		58
10	69	58	52	48	67	58	52	48	57	51	48		56	51	48		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	198208
5°	194563
10°	183475
15°	166494
20°	145636
25°	122862
30°	100598
35°	78032
40°	55847
45°	35353
50°	17637
55°	10781
60°	9298
65°	8561
70°	7565
75°	6947
80°	5935
85°	6038

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 35353 cd/sqm

TEST NUMBER: P1274602

CATALOG NUMBER: P3AS17R709830DE010 E3DLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.5	9.8
10°-20°	204.1	24.2
20°-30°	232.4	27.5
30°-40°	181.7	21.5
40°-50°	89.3	10.6
50°-60°	27.5	3.3
60°-70°	16.3	1.9
70°-80°	8.7	1.0
80°-90°	2.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	519.0	61.4
0°-40°	700.7	82.9
0°-60°	817.5	96.7
0°-90°	845.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	845.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	904	
5°	884	82
15°	733	204
25°	508	232
35°	292	182
45°	114	89
55°	28	27
65°	16	16
75°	8	9
85°	2	3
90°	0	

TEST NUMBER: P1274602

CATALOG NUMBER: P3AS17R709830DE010 E3DLP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	903.9
2.5°	899.2
5°	883.9
7.5°	859.2
10°	824.0
12.5°	782.8
15°	733.4
17.5°	680.6
20°	624.1
22.5°	565.4
25°	507.8
27.5°	451.4
30°	397.3
32.5°	343.2
35°	291.5
37.5°	242.1
40°	195.1
42.5°	151.6
45°	114.0
47.5°	79.9
50°	51.7
52.5°	34.1
55°	28.2
57.5°	24.7
60°	21.2
62.5°	18.8
65°	16.5
67.5°	14.1
70°	11.8
72.5°	9.4
75°	8.2
77.5°	7.1
80°	4.7
82.5°	3.5
85°	2.4
87.5°	1.2
90°	0.0

(END OF REPORT)