

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274618

Luminaire Tested: P3AS20R159830D010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274618
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R159830D010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 98CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 777.0 lumens
Efficiency: N/A
Efficacy: 28.4 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274618
CATALOG NUMBER: P3AS20R159830D010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1274618
 CATALOG NUMBER: P3AS20R159830D010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	97	98	97	95
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	96	94	93	91
3	106	101	97	93	104	99	96	93	97	94	91	94	92	90	92	90	88	92	90	88	87
4	102	96	92	88	100	95	91	88	93	89	87	91	88	86	89	87	85	89	87	85	83
5	98	92	87	84	97	91	87	83	89	86	83	88	84	82	86	83	81	86	83	81	80
6	95	88	83	80	94	87	83	80	86	82	79	85	81	79	83	80	78	83	80	78	77
7	92	85	80	77	91	84	80	76	83	79	76	82	78	76	81	78	75	81	78	75	74
8	89	81	77	74	88	81	77	73	80	76	73	79	75	73	78	75	73	78	75	73	72
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	76	73	70	69
10	84	76	71	68	83	76	71	68	75	71	68	74	71	68	74	70	68	74	70	68	67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	663763
5°	589191
10°	409166
15°	241976
20°	137819
25°	78779
30°	43602
35°	23236
40°	12853
45°	6977
50°	4332
55°	3441
60°	2938
65°	2698
70°	2372
75°	2542
80°	1894
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6977 cd/sqm



TEST NUMBER: P1274618
 CATALOG NUMBER: P3AS20R159830D010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	227.6	29.3
10°-20°	300.4	38.7
20°-30°	154.7	19.9
30°-40°	58.1	7.5
40°-50°	19.0	2.4
50°-60°	8.2	1.1
60°-70°	5.2	0.7
70°-80°	3.0	0.4
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	682.7	87.9
0°-40°	740.8	95.3
0°-60°	768.0	98.8
0°-90°	777.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	777.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3027	
5°	2677	228
15°	1066	300
25°	326	155
35°	87	58
45°	22	19
55°	9	8
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1274618
CATALOG NUMBER: P3AS20R159830D010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	3027.0
1°	3021.0
2°	2981.3
3°	2905.7
4°	2806.2
5°	2676.7
6°	2530.0
7°	2369.1
8°	2190.2
9°	2013.5
10°	1837.6
12.5°	1413.9
15°	1065.9
17.5°	797.9
20°	590.6
22.5°	440.9
25°	325.6
27.5°	237.3
30°	172.2
32.5°	122.0
35°	86.8
37.5°	62.1
40°	44.9
42.5°	32.2
45°	22.5
47.5°	16.5
50°	12.7
52.5°	10.5
55°	9.0
57.5°	7.5
60°	6.7
62.5°	6.0
65°	5.2
67.5°	4.5
70°	3.7
72.5°	3.7
75°	3.0
77.5°	2.2
80°	1.5
82.5°	1.5
85°	0.7
87.5°	0.0
90°	0.0

(END OF REPORT)