

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273642

Luminaire Tested: P3AS09R259830DE010 E3DL1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273642
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R259830DE010 E3DL1H
Description: 3in Adjustable LED luminaire with, R25 optic, 3000K CCT AND, 98CRI , E3DL1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 572.0 lumens
Efficiency: N/A
Efficacy: 52.0 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273642

CATALOG NUMBER: P3AS09R259830DE010 E3DL1H

Luminous Intensity Polar Plot



TEST NUMBER: P1273642

CATALOG NUMBER: P3AS09R259830DE010 E3DL1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	110	105	102	99		107	104	101	98		101	98	96		98	96	94		95	93	92
3	105	100	96	92		103	98	95	91		96	93	90		94	91	89		91	89	87
4	101	95	90	87		99	94	89	86		92	88	85		90	87	84		88	85	83
5	97	90	85	82		96	89	85	81		88	84	81		86	83	80		85	82	79
6	94	86	81	78		92	86	81	78		84	80	77		83	79	77		82	78	76
7	90	83	78	74		89	82	77	74		81	77	74		80	76	73		79	75	73
8	87	79	74	71		86	79	74	71		78	74	71		77	73	70		76	73	70
9	84	76	71	68		83	76	71	68		75	71	68		74	70	68		73	70	67
10	81	73	69	65		80	73	68	65		72	68	65		72	68	65		71	67	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	366922
5°	342328
10°	274232
15°	186153
20°	112640
25°	65859
30°	37499
35°	20639
40°	10963
45°	5768
50°	3343
55°	2523
60°	2149
65°	2283
70°	2116
75°	1864
80°	1389
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5768 cd/sqm

TEST NUMBER: P1273642

CATALOG NUMBER: P3AS09R259830DE010 E3DL1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.0	24.1
10°-20°	225.4	39.4
20°-30°	128.8	22.5
30°-40°	50.8	8.9
40°-50°	15.6	2.7
50°-60°	6.2	1.1
60°-70°	4.1	0.7
70°-80°	2.3	0.4
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	492.2	86.1
0°-40°	543.1	94.9
0°-60°	564.8	98.8
0°-90°	572.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	572.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1673	
5°	1555	138
15°	820	225
25°	272	129
35°	77	51
45°	19	16
55°	7	6
65°	4	4
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1273642

CATALOG NUMBER: P3AS09R259830DE010 E3DL1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	1673.3
1°	1670.0
2°	1656.3
3°	1632.3
4°	1598.9
5°	1555.2
6°	1503.8
7°	1445.9
8°	1378.6
9°	1309.8
10°	1231.6
11°	1154.5
12°	1069.8
13°	986.1
14°	900.3
15°	820.0
17.5°	635.7
20°	482.7
22.5°	362.4
25°	272.2
27.5°	201.7
30°	148.1
32.5°	107.1
35°	77.1
37.5°	54.7
40°	38.3
42.5°	26.2
45°	18.6
47.5°	13.1
50°	9.8
52.5°	7.7
55°	6.6
57.5°	6.0
60°	4.9
62.5°	4.4
65°	4.4
67.5°	3.8
70°	3.3
72.5°	2.7
75°	2.2
77.5°	1.6
80°	1.1
82.5°	1.1
85°	0.5
87.5°	0.5



TEST NUMBER: P1273642
CATALOG NUMBER: P3AS09R259830DE010 E3DL1H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)