

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274623

Luminaire Tested: P3AS20R159830D010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274623
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R159830D010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 98CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1585.0 lumens
Efficiency: N/A
Efficacy: 57.8 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274623

CATALOG NUMBER: P3AS20R159830D010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1274623

CATALOG NUMBER: P3AS20R159830D010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	106	103	100	108	104	101	99	101	99	97		98	96	95		96	94	93	91
3	106	101	97	93	104	99	96	93	97	94	91		94	92	90		92	90	88	87
4	102	96	92	88	100	95	91	88	93	89	87		91	88	86		89	87	85	83
5	98	92	87	84	97	91	87	83	89	85	83		88	84	82		86	83	81	80
6	95	88	83	80	94	87	83	80	86	82	79		85	81	79		83	80	78	77
7	92	85	80	77	91	84	80	76	83	79	76		82	78	76		81	78	75	74
8	89	81	77	74	88	81	77	73	80	76	73		79	75	73		78	75	73	72
9	86	79	74	71	85	78	74	71	77	73	71		77	73	70		76	73	70	69
10	84	76	71	68	83	76	71	68	75	71	68		74	71	68		74	70	68	67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1354014
5°	1201890
10°	834654
15°	493601
20°	281121
25°	160703
30°	88925
35°	47408
40°	26221
45°	14203
50°	8870
55°	6996
60°	6008
65°	5552
70°	4873
75°	5168
80°	3915
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14203 cd/sqm

TEST NUMBER: P1274623

CATALOG NUMBER: P3AS20R159830D010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	464.3	29.3
10°-20°	612.8	38.7
20°-30°	315.5	19.9
30°-40°	118.5	7.5
40°-50°	38.8	2.4
50°-60°	16.7	1.1
60°-70°	10.6	0.7
70°-80°	6.2	0.4
80°-90°	1.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1392.6	87.9
0°-40°	1511.1	95.3
0°-60°	1566.5	98.8
0°-90°	1585.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1585.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6175	
5°	5460	464
15°	2174	613
25°	664	316
35°	177	118
45°	46	39
55°	18	17
65°	11	11
75°	6	6
85°	2	2
90°	0	

TEST NUMBER: P1274623

CATALOG NUMBER: P3AS20R159830D010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	6174.8
1°	6162.5
2°	6081.6
3°	5927.4
4°	5724.3
5°	5460.2
6°	5160.9
7°	4832.6
8°	4467.7
9°	4107.3
10°	3748.5
12.5°	2884.3
15°	2174.3
17.5°	1627.7
20°	1204.7
22.5°	899.3
25°	664.2
27.5°	484.0
30°	351.2
32.5°	248.9
35°	177.1
37.5°	126.7
40°	91.6
42.5°	65.7
45°	45.8
47.5°	33.6
50°	26.0
52.5°	21.4
55°	18.3
57.5°	15.3
60°	13.7
62.5°	12.2
65°	10.7
67.5°	9.2
70°	7.6
72.5°	7.6
75°	6.1
77.5°	4.6
80°	3.1
82.5°	3.1
85°	1.5
87.5°	0.0
90°	0.0

(END OF REPORT)