

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273679

Luminaire Tested: P3AS09R309830DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273679
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R309830DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R30 optic, 3000K CCT AND, 98CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 218.0 lumens
Efficiency: N/A
Efficacy: 19.8 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273679

CATALOG NUMBER: P3AS09R309830DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1273679

CATALOG NUMBER: P3AS09R309830DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		84
4	94	85	79	74	92	84	79	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	51509
5°	50341
10°	46826
15°	41657
20°	35820
25°	30365
30°	25194
35°	19756
40°	14169
45°	9303
50°	5288
55°	3479
60°	3289
65°	3061
70°	2757
75°	2457
80°	2399
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9303 cd/sqm

TEST NUMBER: P1273679

CATALOG NUMBER: P3AS09R309830DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	21.2	9.7
10°-20°	51.0	23.4
20°-30°	57.5	26.4
30°-40°	45.9	21.1
40°-50°	23.6	10.8
50°-60°	8.9	4.1
60°-70°	5.8	2.7
70°-80°	3.1	1.4
80°-90°	0.9	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	129.7	59.5
0°-40°	175.7	80.6
0°-60°	208.2	95.5
0°-90°	218.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	218.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	235	
5°	229	21
15°	184	51
25°	126	57
35°	74	46
45°	30	24
55°	9	9
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1273679

CATALOG NUMBER: P3AS09R309830DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	234.9
1°	234.9
2°	234.1
3°	232.7
4°	230.9
5°	228.7
6°	226.0
7°	222.6
8°	218.8
9°	214.5
10°	210.3
11°	205.4
12°	200.4
13°	195.0
14°	189.4
15°	183.5
17.5°	168.5
20°	153.5
22.5°	139.1
25°	125.5
27.5°	112.1
30°	99.5
32.5°	86.7
35°	73.8
37.5°	61.3
40°	49.5
42.5°	39.1
45°	30.0
47.5°	22.2
50°	15.5
52.5°	11.0
55°	9.1
57.5°	8.3
60°	7.5
62.5°	6.7
65°	5.9
67.5°	5.1
70°	4.3
72.5°	3.5
75°	2.9
77.5°	2.4
80°	1.9
82.5°	1.3
85°	0.8
87.5°	0.3



TEST NUMBER: P1273679

CATALOG NUMBER: P3AS09R309830DE010 E3DLD1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)